

Heat Shrinkable Butt Splice Crimp Connector with Hot Melt Adhesive-lined 0.5 mm² - 1.5 mm² (AWG22-16), Red



Specification

Connector type	: Butt Splice
Termination method	: Crimp
Insulation type	: Fully insulation
Insulation material	: Polyolefin
Insulator color	: Red
Splice sleeve material	: Copper
Splice sleeve plating	: Tin
Wire gauge	: AWG 22-16
Wire cross section	: 0.5 - 1.5 mm ²
Rated current	: 10A max.
Rated temperature	: -20° ~ 125°C
Shrink temperature.	: 150°C ~ 180°C

