

Datasheet

Manufacturer Part No.: T24C013 ... T24C028

Wire ferrules / Twin-wire ferrules 0.5 mm² ... 10 mm² 1000 pcs set



TRU Components wire end ferrules guarantee optimal crimp connections in conjunction with fitting crimping tools. This product series includes wire end ferrules with plastic collars as well as double wire end ferrules in all colors based on the DIN color code. The ferrules are especially suitable for

hobbyists, craftsmen, field service, service workshops, electronics technicians and laboratory needs. Optimal for use with suitable wire end ferrule crimping pliers.

Technical data: Voltage (max.): 440 V, Material: polyamide (collar) / Material: copper • Cross-section: 0.5 mm² ... 10 mm² (AWG: 20 ... 7) • Color: DIN color code • 1000 pcs. bulk-pack.

Part No.	Description	Cross-section	Barrel length	Color	EAN	Content
T24C013	Wire ferrules 0.5 mm ² , plastic-collar white	0.5 mm ²	8 mm	White	4260732286820	1000 pcs
T24C014	Wire ferrules 0.75 mm ² , plastic-collar grey	0.75 mm ²	8 mm	Grey	4260732286837	1000 pcs
T24C015	Wire ferrules 1 mm ² , plastic-collar red	1 mm ²	8 mm	Red	4260732286844	1000 pcs
T24C016	Wire ferrules 1.5 mm ² , plastic-collar black	1.5 mm ²	8 mm	Black	4260732286851	1000 pcs
T24C017	Wire ferrules 2.5 mm ² , plastic-collar blue	2.5 mm ²	8 mm	Blue	4260732286868	1000 pcs
T24C018	Wire ferrules 4 mm ² , plastic-collar grey	4 mm ²	9 mm	Grey	4260732286875	1000 pcs
T24C019	Wire ferrules 6 mm ² , plastic-collar yellow	6 mm ²	12 mm	Yellow	4260732286882	1000 pcs
T24C020	Wire ferrules 10 mm ² , plastic-collar red	10 mm ²	12 mm	Red	4260732286899	1000 pcs
T24C021	Twin-Wire ferrules 0.5 mm ² , plastic-collar white	2x 0.5 mm ²	8 mm	White	4260732286905	1000 pcs
T24C022	Twin-Wire ferrules 0.75 mm ² , plastic-collar grey	2x 0.75 mm ²	8 mm	Grey	4260732286912	1000 pcs
T24C023	Twin-Wire ferrules 1 mm ² , plastic-collar red	2x 1 mm ²	8 mm	Red	4260732286929	1000 pcs
T24C024	Twin-Wire ferrules 1.5 mm ² , plastic-collar black	2x 1.5 mm ²	8 mm	Black	4260732286936	1000 pcs
T24C025	Twin-Wire ferrules 2.5 mm ² , plastic-collar blue	2x 2.5 mm ²	10 mm	Blue	4260732286943	1000 pcs
T24C026	Twin-Wire ferrules 4 mm ² , plastic-collar grey	2x 4 mm ²	12 mm	Grey	4260732286950	1000 pcs
T24C027	Twin-Wire ferrules 6 mm ² , plastic-collar yellow	2x 6 mm ²	14 mm	Yellow	4260732286967	1000 pcs
T24C028	Twin-Wire ferrules 10 mm ² , plastic-collar red	2x 10 mm ²	14 mm	Red	4260732286974	1000 pcs

Connection only by qualified electricians!

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval of the editor. Reprinting, also in part, is prohibited. The publication represents the technical status at the time of printing. All statements without guarantee.

© Conrad Electronic SE