



MCB 10kA 4-pole C-characteristics

Miniature circuit breaker 10kA ideal for industrial and residential applications. It is capable of protecting the system against short-circuit currents up to 10kA. It is equipped with a mounting bracket that allows you to remove or install a miniature circuit-breaker even when the phase busbar is installed and is compatible with all GARO busbars for miniature circuit-breakers. MCB GS C-Characteristic 20A 10kA 4-pole

Common characteristics

Wire flexible [mm²]

1-25

Materials

Plast/Plastic

Degree of protection [IP]

20

Colour

Grå/Grey

Frequency [Hz]

50/60

Package size

3

Rated voltage [V AC]

230/400

Tightening torque [Nm]

3,5

Temperature range [C]

-25...+55

Storage temperature [C]

-35...+55

Modules [pcs]

4

Width [mm]

68

Height [mm]

90

Depth [mm]

75

Specific for 2142769

Name

MCB GS C-KAR 20A 10kA 4P

E-Number

2142769

Article Number

2142769

Type designation

MCB GS C420

Rated current [A]

20

Netweight [kg]

0.42

Poles

4

Rated short-circuit cap. [kA]

10

Connection type

Skruv /Screw

Claim prefuse [A]

125

Tripping characteristics

C

Standard

EN 60898-1

Package size [pcs]

3

Accessories list for MCB 10kA 4-pole C-characteristics

| Name | E-Number | Article Number | Type designation | Article Description |
|-----------------------|----------|----------------|------------------|---|
| HJÄLPKONTAKT F MCB | 2163216 | 110184 | HLPK F MCB | Hjälpkontakt och signalkontakt för dv ärgbry tare typ MCB GR,MCB GS och MCB GQ. |
| LÅSBYGEL | 2163136 | 2163136 | LB 2 | Låsbygel passande MCB GS,RCCB GS,RCBO GS,GCB ,GCBO och de flesta andra komponenter. |