

HSS-HF 1.2-2.4 EL G30M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

General ordering data

Version	Conductor and cable markers, 1.2 - 2.4 mm, green
Order No.	1562940000
Type	HSS-HF 1.2-2.4 EL G30M
GTIN (EAN)	4050118367492
Qty.	1 items

HSS-HF 1.2-2.4 EL G30M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	0.5 mm	Depth (inches)	0.0197 inch
Width	4.2 mm	Width (inches)	0.1654 inch
Length	30000 mm	Length (inches)	1181.1 inch
Net weight	179 g		

Temperatures

Operating temperature range	-55...105 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Type of printing	neutral	Width	4.2 mm
Operating temperature range, max.	105 °C	Operating temperature range, min.	-55 °C
Colour	green	Halogen	No
Length	30000 mm	Basic material	Polyolefine
Printed characters	without	compatible printer	THM MULTIMARK , THM MULTIMARK PLUS
Operating temperature range	-55...105 °C	Number per roll	1

Conductor and cable markers

Halogen	No	Conductor cross-section, max.	0.5 mm ²
Conductor cross-section, min.	0.25 mm ²	Conductor O.D., max.	2.4 mm
Conductor O.D., min.	1.2 mm	Rate of shrinkage	2:1
Recommended shrinking temperature	90 °C	Conductor O.D.	1.2 - 2.4 mm
Cross-section for connected wire	0.25 - 0.5 mm ²		

Important note

Product information	External roll holder 1302920000 necessary
---------------------	---

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02
ECLASS 13.0	27-28-11-02	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		



HSS-HF 1.2-2.4 EL G30M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany


www.weidmueller.com

Accessories
Ink ribbons


These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON HSS HF EL 40/300...	Version
Order No.	1426210000	Ink ribbon
GTIN (EAN)	4050118228823	
Qty.	1 ST	

THM MULTIMARK


These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	THM MMP EXT.RH	Version
Order No.	1302920000	
GTIN (EAN)	4050118102307	
Qty.	1 ST	
Type	MULTIMARK ROLLER 115	Version
Order No.	1357420000	
GTIN (EAN)	4050118160314	
Qty.	1 ST	
Type	MULTIMARK ROLLER 30	Version
Order No.	1357430000	
GTIN (EAN)	4050118160253	
Qty.	1 ST	


HSS-HF 1.2-2.4 EL G30M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

THM MULTIMARK PLUS



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	MULTIMARK PLUS ROLLER 1...	Version
Order No.	2672590000	
GTIN (EAN)	4050118708097	
Qty.	1 ST	