

## Technical Specifications – PowerTray and PowerTrolley (all variants)

Model	PT1025 with 3x F2C10	PT1025 with 3x F2CS10	PT1025 with 2x F25C10	PT1025 with 2x F25CS10	PT1025 trolley with no trays
Sync capability	No	Yes	No	Yes	N/A
Weight	37.7kg	37.7kg	35.8Kg	35.8Kg	29kg
Approx Shipping Dimensions	Shipped on a pallet 600mm (H) x 1200mm (W) x 1000mm (D)				
Approx Shipping Weight	63.5 Kg		60 Kg		50 Kg
Package contents	PowerTrolley and 3 PowerTrays		PowerTrolley and 2 PowerTrays		PowerTrolley
Cooling Ventilation	1 x 5V fan per tray		1 x 5V fan per tray		Air Vents
Materials	Flame retardant polypropylene, Powder coated steel				Steel
Overall Trolley Dimensions	Height 790mm x Width 423mm x Depth 545mm				
Max ambient operating temperature	30° C				
Warranty	2 Years				
Colour	Silver, White, Blue, Pink, Yellow				
Country of origin	United Kingdom				
Max loaded weight per tray	Maximum weight of the 10 devices must not exceed 5kg				
Maximum Device Size (including any case) when stored in a tray within a trolley	H290mm x W190mm x D21mm for F2 Tray H290mm x W290mm x D21mm for F25 Tray				

Model	F2C10	F2CS10	F25C10	F25CS10
Sync capability	No	Yes	No	Yes
Tray Dimensions	H150 x W312 x L427		H225 x W312 x L430	
Tray weight without devices	2.9 kg		3.4Kg	
Approx Shipping Dimensions	H265mm x W520mm x D346mm			
Approx Shipping Weight	4.5Kg		5 Kg	
Maximum Device Size (including any case) when stored in a tray within a trolley	H290mm x W190mm x D21mm for F2 Tray H290mm x W290mm x D21mm for F25 Tray			
Capacity	10 USB Devices			
Cooling Ventilation	1 x 5V fan per tray			
Input/output	220-240V, 0.8A Max, 50-60HZ / 5.2V, 2.1A max per port			
Max loaded weight per tray	Maximum weight of the 10 devices must not exceed 5KG			
Certification of PowerTray models F2C10, F2CS10, F25C10, F25CS10	CE, CB, RoHS compliant. EMC: Emissions standard: EN61000-6-3:2007+A1:2011 Immunity standard: EN61000-6-1:2007 CB SCHEME, TO THE REQUIREMENTS OF: IEC 60950-1: 2005+A2: 2013 EN 60950-1: 2006+A2: 2013 Including national differences for Denmark, Norway, Sweden, Finland, United Kingdom, Rep of Ireland, Switzerland & Spain.			
Max ambient operating temperature	30° C			
Materials	Flame retardant Polypropylene, Powder coated steel			
Warranty	2 Years			
Colour	White			
Country of origin	United Kingdom			
Package contents	Tray, lid, power cord set and documentation. (Sync cable provided with Sync devices only)			