

**SAI-TMCGK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Weidmüller offers a wide range of tools and accessories for sensor-actuator cabling.

**General ordering data**

|            |                               |
|------------|-------------------------------|
|            |                               |
| Version    | Pressing tool, 4-indent crimp |
| Order No.  | <a href="#">1381670000</a>    |
| Type       | SAI-TMCGK                     |
| GTIN (EAN) | 4050118183757                 |
| Qty.       | 1 items                       |

## SAI-TMCGK

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Dimensions and weights

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Length     | 178 mm | Length (inches) | 7.0079 inch |
| Net weight | 634 g  |                 |             |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## Technical data

|         |                                             |
|---------|---------------------------------------------|
| Version | Mechanical, without interchangeable inserts |
|---------|---------------------------------------------|

## Description of contact

|                                   |                 |                                   |        |
|-----------------------------------|-----------------|-----------------------------------|--------|
| Type of contact                   | Turned contacts | Conductor cross-section, max. AWG | AWG 26 |
| Conductor cross-section, min. AWG | AWG 12          |                                   |        |

## tool data crimping

|                                       |                      |                                       |                      |
|---------------------------------------|----------------------|---------------------------------------|----------------------|
| Wire end ferrules cross-section, max. | 0.82 mm <sup>2</sup> | Wire end ferrules cross-section, min. | 0.08 mm <sup>2</sup> |
| Crimping type/profile                 | 4-indent crimp       |                                       |                      |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000168    | ETIM 7.0    | EC000168    |
| ETIM 8.0    | EC000168    | ETIM 9.0    | EC000168    |
| ETIM 10.0   | EC000168    | ECLASS 9.0  | 21-04-38-11 |
| ECLASS 9.1  | 21-04-38-11 | ECLASS 10.0 | 21-04-38-11 |
| ECLASS 11.0 | 21-04-38-11 | ECLASS 12.0 | 21-04-38-11 |
| ECLASS 13.0 | 21-04-38-11 | ECLASS 14.0 | 21-04-38-11 |
| ECLASS 15.0 | 21-04-38-11 |             |             |