

IE-CT-SC-GOF-P

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

GOF

- For fibre-optic SC/ST, IP 20 and IP 67 connectors
- For fibre-optic LC and IP 67 connectors

POF

- For polymer fibre-optic SC/ST, IP 20 and IP 67 connectors
- For fibre-optic, Profinet and Mobil cable SC/ST and IP 67 connectors

General ordering data

Version	Pressing tool, Hexagonal crimp
Order No.	9205350000
Type	IE-CT-SC-GOF-P
GTIN (EAN)	4032248725489
Qty.	1 items

IE-CT-SC-GOF-P

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Width	250 mm	Width (inches)	9.8425 inch
Net weight	624.8 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

Technical data

Description of article	Crimping tool for fibre-optic, ProfiNet, Mobil cable SC/ST and IP 67 connectors	Version	Mechanical, without interchangeable inserts
------------------------	---	---------	---

tool data crimping

Crimping type/profile	Hexagonal crimp
-----------------------	-----------------

Classifications

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ETIM 9.0	EC000168
ETIM 10.0	EC000168	ECLASS 9.0	21-04-38-11
ECLASS 9.1	21-04-38-11	ECLASS 10.0	21-04-38-11
ECLASS 11.0	21-04-38-11	ECLASS 12.0	21-04-38-11
ECLASS 13.0	21-04-38-11	ECLASS 14.0	21-04-38-11
ECLASS 15.0	21-04-38-11		