

ESG-LP 6/15 MM SI**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germanywww.weidmueller.com**Guaranteed long service life: ESG**

The multi-colour and multi-format labels have a strong adhesive layer to ensure the best possible adhesion to the underlying surface. Double laminated polyester makes the basic material very thin and yet extremely tear-resistant.

Your benefits with MultiMark

- “Different materials for various requirements”
- Can be used with equipment from many manufacturers
- Device markers with a familiar design

General ordering data

Version	ESG, Device markers, 6 x 15 mm, silver
Order No.	2711860000
Type	ESG-LP 6/15 MM SI
GTIN (EAN)	4050118750072
Qty.	24000 items

ESG-LP 6/15 MM SI

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	0.05 mm	Depth (inches)	0.002 inch
Height	6 mm	Height (inches)	0.2362 inch
Width	15 mm	Width (inches)	0.5906 inch
Net weight	0.02 g		

Temperatures

Operating temperature range	-40...150 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Adhesive	Acrylate adhesive	Version	Self-adhesive, halogen-free
Width	15 mm	UL 94 flammability rating	V-0
Operating temperature range, max.	150 °C	Operating temperature range, min.	-40 °C
Colour	silver	Halogen	No
Basic material	Polyester	Printed characters	without
Size of labelling field	6 x 15 mm	Approval acc. to UL 969	Yes
compatible printer	THM MULTIMARK LPC	Operating temperature range	-40...150 °C

Device markers

Halogen	No
---------	----

Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 9.0	27-40-06-29
ECLASS 9.1	27-40-06-29	ECLASS 10.0	27-40-06-29
ECLASS 11.0	27-28-11-04	ECLASS 12.0	27-28-11-04
ECLASS 13.0	27-28-11-04	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		




ESG-LP 6/15 MM SI**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germanywww.weidmueller.com**Accessories****Ink ribbons**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON MM-TB 25/360 SW	Version	
Order No.	2005090000	Ink ribbon	
GTIN (EAN)	4050118390216		
Qty.	1 ST		

THM MULTIMARK

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	THM MMP EXT.RH	Version	
Order No.	1302920000		
GTIN (EAN)	4050118102307		
Qty.	1 ST		