

GWDR PG48-NP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	GWDR NP (flat gasket - neoprene), Sealing ring, PG 48, Neoprene
Order No.	1719630000
Type	GWDR PG48-NP
GTIN (EAN)	4008190352899
Qty.	5 items

GWDR PG48-NP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Height	1.5 mm	Height (inches)	0.0591 inch
Net weight	4 g		

Temperatures

Operating temperature	-40 °C... 100 °C
-----------------------	------------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General information

Silicone	No	Number of wires	1
O.D.	71 mm	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Thickness	1.50 mm
Cable gland	PG 48	Basic material	Neoprene
Diameter of sealing ring	71.00 mm	Sealing	Neoprene
External thread	PG 48	Internal thread	PG 48
Inside diameter D2	59.30 mm		

Classifications

ETIM 6.0	EC001181	ETIM 7.0	EC001181
ETIM 8.0	EC001181	ETIM 9.0	EC001181
ETIM 10.0	EC001181	ECLASS 9.0	27-43-03-19
ECLASS 9.1	27-14-44-90	ECLASS 10.0	27-43-03-19
ECLASS 11.0	27-43-03-19	ECLASS 12.0	27-43-03-19
ECLASS 13.0	27-43-03-19	ECLASS 14.0	27-43-03-19
ECLASS 15.0	27-43-03-19		

Drawings

