





Led Color	Lens Color	VF	IF	Viewing Angle	Mcd	Mounting Hole	Circuit Diagram
White	Water Clear	3.2V	20mA	15°	8000	 Panel Thickness: 5.0 max	
Insulation Resistance		DC500V 100M OHM Min					
Dielectric Strength		AC500V 1 Minute					
Operation Temperature		-25°C~+85°C					



Remark:
 1. LED Type: $\phi 5\text{mm}$
 2. Unless Otherwise Specified
 All Tolerances To Be ± 0.2
 3. ROHS Compliant

Date	Name	Descriptions				△
Drawn	Checked	Approved	SCI No.	Model Name	LED Indicator Light	NO
鍾運穎	研發部		Customer No.	Model No.	R9-104L-12-W	
06.18.'07	李元生		Unit	mm	SHIN CHIN INDUSTRIAL CO., LTD.	