

Data Sheet

BNC socket - BNC plug

Cable category: RG 59 B/U
Connection: Crimp
Impedance: 75 Ω
Cable dia.: 3.90 mm
Closure type: Bayonet
Material (details): Brass, nickel plated
Connector type: Plug, straight
Insulation material: PTFE
Product type: BNC Connector

