

BU-34X

(Stainless Steel, Micro Alligator Clip)



DESCRIPTION:

The BU-34X Clip is intended for applications where plated carbon steel or solid copper clips are not effective.

Dimensions: Length: 1.1" (28 mm); Width: .20" (5.1 mm); Height: .31" (7.9 mm)

Jaw Nose Width is .06" (1.5mm)

Jaw opens to: .22" (5.6 mm)

Connection: Solder (Wire up to 18 AWG can be used). Note, stainless steel can be very difficult to

solder. Mueller recommends using a flux designed for stainless steel.

Material: Clip – 304 stainless steel, Spring – 302 stainless steel, Rivet – 302 Stainless Steel

Ratings: 5 Amps

Insulators: Purchased separately. Uses BU-36-* Insulators.

RoHS Compliant

Toll Free: 800.955.2629

Phone: 330.780.2525

Fax: 330.780.2524