
GP Batteries

DATA SHEET


Description	: Consumer Lithium Battery, CR2 Pro		
Chemical System	: Lithium Manganese Dioxide		
Nominal Voltage	: 3.0 Volts		
Nominal Capacity	: 800mAh @ 10mA to 1.8V at 23°C		
Dimensions	: Ø15.3 mm x 26.5 mm		
Terminals	: Flat		
Shelf Life	: Up to 10 years		
Average Weight	: App. 10g		
Application	: Smoke Detector, Sensors, Home Security Products		
Operating Temperature	:-40°C to +60°C		
Standards	: UL1642, UL2054, IEC60086-4, UN38.3		




Cross References:

JIS	GP	Panasonic	Energizer	Duracell
CR15H270	CR2	CR-2	EL1CR2	DLCR2

Discharge Characteristics 900mA, 3 seconds on / 27 seconds off



Continuous Discharge at 23°C



The information (subject to change without prior notice) contained in this document is for reference only and should not be used as a basis for product guarantee or warranty. For applications other than those described here, please consult your nearest GP Sales and Marketing Office or Distributors.

www.gpbatteries.com