

Specification:

Material:

Plastic material: polypropylene

Flammability rating: UL94 HB, UL File No. E216959

Temperature range: -10°C to $+100^{\circ}\text{C}$

Springs: nickel plated spring steel

Wire: 152.4mm Long 26AWG UL1007, CSA - TR-64, 300V, 80°C

Rivets: brass, nickel plated

9 volts snaps: brass nickel plated

Contact resistance: under 50mΩ for +/– contacts per EIA-540J000

RoHS compliant

Tolerances	mm (inches)
Decimal	±0.5 (0.020)
Fractional	±0.8 (0.030)
Angular	±3°

ORDERING CODE BC4AA

SOLDER LUGS	= L
(6in) WIRE LEADS	= W
9 VOLT TYPE SNAPS	= S
PC PINS	= P

