Batteries

DATA SHEET


NO MERCURY ADDED					
Description	: Mercury Free Extra Heavy Duty				
	Battery, C Size				
Chemical System	: Zinc Chloride				
Nominal Voltage	: 1.5 Volts				
Nominal Dimensions	: ø26.2 mm x 50 mm				
Terminals	: Protruded positive (+) and flat				
	negative (-) contacts				
Jacket	: Metal jacket with PVC insulation				
Applications	: All electronic devices, e.g. transistor				
	radios, cassette recorders, toys,				
	alarm clocks, lighting, torches &				
	portable fans.				
Warranty Period	: 36 months				
Average Weight	: 47.8g				

Cross References:


GP	JIS	IEC	Eveready
14G	R14P	R14P	1235


Typical Service Life:

Discharge	Discharge	End Point	Service
Resistance	Condition	Voltage	Life
3.9 Ohms	1 Hr/ Day	0.8V	8.2 Hrs



Model No.: GP14G





Unit: mm

The information (subject to change without prior notice) contained in this document is for reference only and should not be used as a basis for product guarantee or warranty. For applications other than those described here, please consult your nearest GP Sales and Marketing Office or Distributors.

www.gpbatteries.com