



Material - Safety - Data Sheet (MSDS)

for

Ansmann Alkaline (Manganese Dioxide) Batteries

single cells, multi-cell batteries and battery packs

No.15

1/6

Date of issue: 2011 - 06 - 18
Revision no: 12
Revision date: 2024 - 03 - 05
Editor: Ansmann AG

The information contained within is provided as a service to our customers and for their information only. The information and recommendations set forth herein are made in good faith and are believed to be accurate at the date of preparation. ANSMANN AG makes no warranty expressed or implied.

1. Product and Supplier Identification

Product name: ANSMANN X-Power / Red Line / HyCell / Industrial / Premium - Alkaline Battery
Designation: Alkaline Battery
Models / types: LR6 (AA); LR03 (AAA); LR14 (C), LR20(D); LR1; 6LR61 (9V E-block); LR61 (AAAA)

Electrochemical system: MnO₂ (Manganese Dioxide) (positive electrode)
Zn (negative electrode)
KOH (electrolyte)

Supplier:
Germany ANSMANN AG
Address: Industriestraße 10; 97959 Assamstadt; Germany
Phone / Fax: + 49 (0) 6294 42040 / + 49 (0) 6294 420444
Home / email: ansmann.de / info@ansmann.de

Subsidiaries:

United Kingdom ANSMANN UK LTD.
Address: Units 11-12, RO24, Harlow Business Park, Harlow, Essex. CM19 5QB. UK
Phone / Facsimile: +44 (0) 870 609 2233 / +44 (0) 870609 2234
email: UK@ansmann.de

Hong Kong ANSMANN Energy Int. LTD.
Address: Unit 3117-18, 31/F; Tower 1; Millenium City 1; No. 388 Kwun Tong Road;
Kwun Tong, kowloon; Hong-Kong
hongkong@ansmann.de

China HuiZhou City ANSMANN Trading Co. LTD
Address: Da Lian Industrial Park, Rengtu Village Ruhu Town Huicheng District,
516169 Huizhou City Guangdong, China
china@ansmann.de

Sweden ANSMANN Nordic AB
Address: Victor Hasselblads Gata 11, 421 31 Västra Frölunda, Sweden
nordic@ansmann.de

France Ansmann Energy France
Address: 5, Place Copernic; Immeuble Boréal - Courcouronnes; F-91023 Evry Cedex;
France

EMERGENCY CONTACT: For chemical emergency (spill, leak, fire, exposure or accident)
call phone no.: +49 6294 4204 0

2. Product and Supplier Identification

The Alkaline batteries described in this MSDS are hermetically sealed units, which are not hazardous when used according to the recommendations of the manufacturer. Under normal condition of use of the batteries, the electrode materials and the liquid electrolyte they contain are non-reactive provided the battery integrity is maintained. Risk of exposure exists only in case of mechanical, electrical or thermal abuse. Thus the batteries should not short circuited, recharged, punctured, incinerated, crushed, immersed in water, force discharged or exposed to temperatures above the temperature range of the cell or battery. In these cases there is risk of fire or explosion.



Material - Safety - Data Sheet (MSDS)

for

Ansmann Alkaline (Manganese Dioxide) Batteries

single cells, multi-cell batteries and battery packs

No.15

2/6

3. Composition and Informations on Ingredients

IMPORTANT NOTE: The product is a manufactured article as described in 29 CFR 1910.1200. The battery cell is contained in a hermetically-sealed case, designed to withstand temperatures and pressures encountered during normal use. As a result, during normal use, hazardous materials are fully contained inside the battery cell. The battery cell should not be opened or exposed to heat because exposure to the following ingredients contained within could be harmful under some circumstances. The following information is provided for the user's information only.

Ingredient	Content	CAS No.	Hazard Symbols	Hazard Statements
Manganese Dioxide (MnO ₂)	30 - 50%	1313-13-9		H302
Graphite (C)	2 - 6%	7782-42-5		H228, H319, H335
Zinc (Zn) Zinc Oxide (ZnO)	10 - 25% < 1%	7440-66-6 1314-13-2		H410
Potassium Hydroxide (KOH)	2 - 16%	1310-58-3		H302 H314
Brass	0 - 5%	12597-71-6		-
Stainless Steel (Fe)	15 - 30%	7439-89-6		-
Lead (Pb) Cadmium (Cd) Mercury (Hg) see chapter no.12	< 0.004% < 0.0003% < 0.0005%	7439-92-1 7440-43-9 7439-97-6		
Paper, Water, Plastic	residue			

4. First Aid Measures

Inhalation:	If battery is leaking, contents may be irritating to respiratory passages. Move to fresh air. If irritation persists, seek medical advice.
Skin Contact:	Wash off skin thoroughly with water. Remove contaminated clothing and wash before re-use. In severe cases obtain medical attention.
Eye Contact:	Irrigate thoroughly with water for at least 15 minutes. Lifting upper and lower lids, until no evidence of the chemical remains. Obtain medical attention.
Ingestion:	Wash out mouth thoroughly with water. Do not induce vomiting or give food or drink. Seek medical attention immediately.
Further treatment:	All cases of eye contamination, persistent skin irritation and casualties who have swallowed this substance or been affected by breathing its vapours should be seen by a doctor.

5. Fire Fighting Measures

Fire and explosion hazards:	Batteries may burst and release hazardous decomposition products when exposed to a fire situation.
Suitable extinguishing media:	Use foam, dry powder, carbon dioxide (CO ₂), as appropriate
Extinguishing media with limited suitability:	Water is only applicable for incipient fire.
Special fire fighting procedures:	Firefighters should wear positive pressure self-contained breathing apparatus and full protective clothing. Fight fire from a distance or protected area.



Material - Safety - Data Sheet (MSDS)

for

Ansmann Alkaline (Manganese Dioxide) Batteries

single cells, multi-cell batteries and battery packs

No.15

3/6

Hazardous combustion products:

Thermal degradation may produce hazardous fumes of zinc and manganese, hydrogen gas, caustic vapors of potassium hydroxide and other toxic by-products.

6. Accidental Release Measures

Notify safety personnel of large spills. Caustic potassium hydroxide may be released from leaking or ruptured batteries. Clean-up personnel should wear appropriate protective clothing to avoid eye and skin contact and inhalation of vapors or fumes. Increase ventilation. Carefully collect batteries and place in an appropriate container for disposal.

7. Precautions for safe Handling and Use

Storage:

Store batteries in a dry place at normal room temperature.
Do not refrigerate – this will not make them last longer.
Elevated temperatures can result in shortened battery life. Temperatures above 100°C may result in battery leakage and rupture.

Mechanical Containment:

If potting or sealing the battery in an airtight or watertight container is required, consult Ansmann AG representative for precautionary suggestions. Do not obstruct safety release vents on batteries. Encapsulation of batteries will not allow cell venting and can cause high pressure rupture.

Handling:

Avoid mechanical or electrical abuse. DO NOT short circuit or install incorrectly. Batteries may explode, pyrolyze or vent if disassembled, crushed, recharged or exposed to high temperatures. Install batteries in accordance with equipment instructions. Do not mix battery systems, such as alkaline and zinc carbon, in the same equipment. Replace all batteries in equipment at the same time. Do not carry batteries loose in a pocket or bag. Do not remove the battery label.

Charging:

Do not charge this batteries! This battery type is manufactured in a ready-to-use-state. It is not designed for recharging.

Recharging can cause battery leakage, or in some cases, can cause the safety release vent to open. Inadvertent charging can occur if a battery is installed backwards.

Disposal:

Dispose in accordance with all applicable federal, state and local regulations.

8. Special Protection Information

Ventilation Requirements:

Not necessary under normal conditions. Room ventilation may be required in areas where there are open or leaking batteries.

Respiratory Protection:



Not necessary under normal conditions. Avoid exposure to electrolyte fumes from open or leaking battery. In all fire situations, use self-contained breathing apparatus

Eye Protection:



Not necessary under normal conditions. Wear safety glasses with side shields if handling an open or leaking battery.

Hand Protection:



Not necessary under normal conditions. Use neoprene or natural rubber gloves if handling an open or leaking battery

9. Physical and Chemical Properties

Appearance: small round cylinders

Odour: n/a

Vapour Density: n/a

Vapour Pressure: n/a

Boiling Point: n/a

VOC Content: n/a

Evaporation Rate: n/a

Solubility in Water: n/a

Specific Gravity: not determined

pH: not determined



Material - Safety - Data Sheet (MSDS)

for

Ansmann Alkaline (Manganese Dioxide) Batteries

single cells, multi-cell batteries and battery packs

No.15

4/6

10. Stability and Reactivity

Product is stable under conditions described in Section 7.

Conditions to avoid: Heat above 100° or incinerate. Deform. Mutilate. Crush. Pierce. Disassemble. Recharge. Short circuit. Expose over a long period to humid conditions.

Hazardous decomposition products: Thermal decomposition may produce hazardous fumes of zinc and manganese; caustic vapors of potassium hydroxide and other toxic by-products.

Hazardous polymerization: Will not occur.

11. Toxicological Information

Potential Health Effects: The chemicals and metals in this product are contained in a sealed can. Exposure to the contents will not occur unless the battery leaks, is exposed to high temperatures or is mechanically, physically, or electrically abused. Damaged battery will release concentrated potassium hydroxide, which is caustic. Anticipated potential leakage of potassium hydroxide is up to 20 ml, depending on battery size. A similar amount of zinc may also leak.

Inhalation: Inhalation of vapors or fumes released due to heat or a large number of leaking batteries may cause respiratory and eye irritation.

Skin contact: Contact with battery contents may cause severe irritation and burns.

Eye contact: Contact with battery contents may cause severe irritation and burns. Eye damage is possible.

Ingestion: For big Alkaline batteries (e.g. D, C, AA-size) swallowing is not anticipated due to battery size. Choking may occur if smaller batteries are swallowed. Ingestion of battery contents (from a leaking battery) may cause mouth, throat and intestinal burns and damage.

Acute Toxicity Data: Manganese Dioxide: LD50 oral rat >3478 mg/kg
Potassium Hydroxide: LD50 oral rat 273 mg/kg

Chronic Effects: The chemicals in this product are contained in a sealed can and exposure does not occur during normal handling and use. No chronic effects would be expected from handling a leaking battery.

Target Organs: Skin, eyes and respiratory system.

Carcinogenicity: None of the components of this product are listed as carcinogens by the EU Directive on the classification and labeling of substances.

12. Ecological Information

ANSMANN primary alkaline cells / batteries described in this MSDS do not contain heavy metals as defined by the European Directive 2006/66/EC Article 21; they comply with the chemical composition requirements of this directive.

Mercury has not been "intentionally introduced (as distinguished from mercury that may be incidentally present in other materials)" in the sense of the USA "Mercury-Containing and Rechargeable Battery Management Act" (May 13 1996).

The Regulation on Mercury Content Limitation for Batteries promulgated on 1997-12-31 by the China authorities including the State Administration of Light Industry and the State Environmental Protection Administration defines 'low mercury' as 'mercury content by weight in battery as less than 0.025%' , and mercury free' as 'mercury content by weight in battery as less than 0.0001%'. And therefore: Ansmann cylindrical primary alkaline cells/batteries belong to the category of mercury-free battery (mercury content lower than 0.0001%).



Material - Safety - Data Sheet (MSDS)

for

Ansmann Alkaline (Manganese Dioxide) Batteries

single cells, multi-cell batteries and battery packs

No.15

5/6

13. Disposal Information

Do not incinerate, recharge, disassemble short, or subject cells to temperatures in excess of 100°C. Such abuse can result in loss of seal, leakage, and / or cell explosion.

In order to avoid short circuit and heating, used Ansmann primary alkaline cells / batteries should never be stored or transported in bulk. Proper measures against short circuit are:

- Storage of batteries in original packaging
- Coverage of the terminals

Dispose of in accordance with appropriate national and local regulations.

USA: Primary alkaline batteries (manganese-dioxide batteries) are classified by the federal government as non-hazardous waste and are safe for disposal in the normal municipal waste stream.

In the European Union, manufacturing, handling and disposal of batteries is regulated on the basis of the DIRECTIVE 2006/66/EC OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 6 September 2006 on batteries and accumulators and waste batteries and accumulators and repealing Directive 91/157/EEC. Customers find detailed information on disposal in their specific countries using the web site of the European Portable Batteries Association (http://www.epbaeurope.net/legislation_national.html)

Importers and users outside EU should consider the local laws and rules.

14. Transport Information

The described ANSMANN primary alkaline cells / batteries are considered to be "dry cell" batteries and are unregulated for purposes of transportation by the U.S. Department of Transportation (DOT), International Civil Aviation Administration (ICAO), International Air Transport Association (IATA), the International Maritime Organization (IMO), the "Accord Européen Relatif au Transport International des Marchandises Dangereuses par Route" (ADR) and the "Règlement concernant le transport international ferroviaire de marchandises Dangereuses" (RID).

IATA DGR: Special Provision A123: "Examples of such batteries are: alkali-manganese, zinc-carbon and nickel-cadmium batteries. Any electrical battery...having the potential of a dangerous evolution of heat must be prepared for transport as to prevent:

- (a) a short circuit (e.g. in the case of batteries, by the effective insulation of exposed terminals...)
- (b) an accidental activation

The words "Not Restricted" and the Special Provision number must be included in the description of the substance on the Air Waybill as required by 8.2.6, when an Air Waybill is issued.

EU: As primary alkaline cells/batteries are not explicitly mentioned in RID/ADR, there are no special Dangerous Goods shipment requirements for these products.

USA: 49 CFR § 172.102 Special Provision 130: "For other than a dry battery specifically covered by another entry in the § 172.101. table, "Batteries, dry" are not subject to the requirements of this subchapter when they are securely packaged and offered for transportation in a manner that prevents the dangerous evolution of heat (for example, by the effective insulation of exposed terminals) and protects against short circuits".

Code of practice for packaging and shipment of primary batteries given in IEC 60086-1: The packaging shall be adequate to avoid mechanical damage during transport, handling and stacking. The materials and pack design shall be chosen so as to prevent the development of unintentional electrical conduction, corrosion of the terminals and ingress of moisture. Shock and vibration shall be kept to a minimum. For instance, boxes should not be thrown off trucks, slammed into position or piled so high as to overload battery containers below. protection from inclement weather should be provided.



Material - Safety - Data Sheet (MSDS)

for

Ansmann Alkaline (Manganese Dioxide) Batteries

single cells, multi-cell batteries and battery packs

No.15

6/6

15. Regulatory Information

Marking consideration: According to Directive 2006/66/EC of THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 6 September 2006 on batteries and accumulators and waste batteries and accumulators and repealing Directive 91/157/EEC primary alkaline cylindrical cells/batteries of size LR6, LR14, LR20, LR1 and 6LR61 have to be marked with the crossed bin on the battery casing, those of size LR03 have to be marked with the crossed bin on the packaging.

Water hazard class: (according to German Federal Water Management Act)
non-water pollution according to VwVwS Appendix 1

16. Other Information

Full text of Hazard Statements referred to under section 3

H228	Flammable solid
H302	Harmful if swallowed
H314	Causes severe skin burns and eye damage
H319	Causes serious eye irritation
H332	Harmful if inhaled
H335	May cause respiratory irritation
H410	Very toxic to aquatic life with long lasting effects

This information has been compiled from sources considered to be dependable and is, to the best of our knowledge and belief, accurate and reliable as of the date compiled. However, no representation, warranty (either expressed or implied) or guarantee is made to the accuracy, reliability or completeness of the information contained herein.

This information relates to the specific materials designated and may not be valid for such material used in combination with any other materials or in any process. It is the user's responsibility to satisfy himself as to the suitability and completeness of this information for his particular use.

Ansmann AG does not accept liability for any loss or damage that may occur, whether direct, indirect, incidental or consequential, from the use of this information. Ansmann AG does not offer warranty against patent infringement