


Yucel-Series - Valve Regulated Lead Acid Battery

Y24-12

SPECIFICATIONS		
Nominal voltage	12	V
20-hr rate Capacity to 1.75VPC at 20°C	24	Ah
10-hr rate Capacity to 1.75VPC at 20°C	22.23	Ah
DIMENSIONS		
Length	166.5 (±1)	mm
Width	175 (±1)	mm
Height	125 (±1)	mm
(height over terminals)	125 (±2)	mm
Mass (typical)	8.1	kg
TERMINAL TYPE		
Female threaded terminal	M5	
Torque (Nm)	2.0~3.0	Nm
OPERATING TEMPERATURE RANGE		
Storage	-20°C to +60°C	
Charge	-15°C to +50°C	
Discharge	-20°C to +60°C	
STORAGE		
Capacity loss per month at 20°C (approx)	3	%
CASE MATERIAL		
Standard Option	ABS (UL.94:HB)	
Flame retardant option (FR)	ABS (UL94:V0)	
CHARGE VOLTAGE		
Float charge voltage at 20°C	13.65 (±1%)	V
	2.275 (±1%)	V/cell
Float Charge voltage temperature correction factor (for variations from the standard 20°C)	-3	mV/cell/°C
Cyclic (or Boost) charge at 20°C	14.5 (±3%)	V
	2.42 (±3%)	V/cell
Cyclic Charge voltage temperature correction factor (for variations from the standard 20°C)	-4	mV/cell/°C
CHARGE CURRENT		
Float charge current limit	No limit	A
Cyclic (or Boost) charge current limit	6	A
MAXIMUM DISCHARGE CURRENT		
1 minute	48	A
SHORT-CIRCUIT CURRENT & INTERNAL RESISTANCE (according to EN IEC 60896-21)		
Internal resistance	N/A	mΩ
Short-Circuit current	N/A	A
IMPEDANCE		
Measured at 1 kHz	14	mΩ
PERFORMANCE & CHARACTERISTICS		
Refer to the technical manual	YUCEL	
DESIGN LIFE		
EUROBAT Classification: Standard Commercial	3 to 5	years
Yuasa design life @ 20°C	up to 5	years
SAFETY		
Installation		
Can be installed and operated in any orientation except permanently inverted		
Handles		
Batteries must not be suspended by their handles (where fitted)		
Vent valves		
Each cell is fitted with a low pressure release valve to allow gasses to escape and then reseal.		
Gas Release		
VRLA Batteries release hydrogen gas which can form explosive mixtures in air. Do not place inside a sealed container		
Recycling		
YUASA's VRLA batteries must be recycled at the end of life in accordance with local and national laws and regulations		

Data Sheet



3RD PARTY CERTIFICATIONS

ISO 9001 - Quality Management Systems
 ISO 14001 - Environmental Management Systems
 EN 18001 - OHSAS Management Systems
 UNDERWRITERS LABORATORIES Inc.



STANDARDS

IEC61056



ALL DATA IS SUBJECT TO CHANGE WITHOUT NOTICE

Issue No.: V.1 / Issue Date: July 2010



YUASA BATTERY SALES UK LTD.
 Unit 22
 Rassau Industrial Estate
 Ebbw Vale, Gwent
 NP23 5SD
 UK