





No. of Positions

No.	A	B	C	D
50	68.18	60.96	62.23	3.80



Specifications:

Current Rating:1.0 Amp

Contact resistance:30m Ohm Max. at 6V DC 0.3A

Insulator resistance:1000M ohm min. at 500V DC

Withstanding Voltage:500V AC/Minute

Operating Temperature Range:-40°~+105°C

Wire Size Flat Cable I.D.C: 1.27mm Pitch

AWG#28(standard 0.20mm) OR #30 (0.17mm).

Material And Finish

Insulator:PBT&Glass—fiber reinforced UL94V-0

Insulator Color:Black or Gray

Contact:Phosphor Bronze or Brass

Contact Plating:See Contact Plating Tab.

Note:(*)Marked is Important DIM For QC.

1. CONTACT MATERIAL & SR OPTION:

WITH BUMP (NOSE):

"DC" BRASS WITH STRAIN RELIEF

3. CONTACT FINISH:

"S" SELECTIVE GOLD PLATED

4. INSULATOR COLOR:

"B" BLACK (STANDARD)