

Datasheet

SPECIFICATIONS: TC-D17-xxASA2-G

Material

Insulator : PBT, glass reinforced, rated UL 94V-0

Contact : Brass

Electrical

Current Rating : 1 Amp

Contact Resistance : 30 mΩ max.



Insulation Resistance : 3000 MΩ min.

Dielectric Withstanding Voltage : 500V AC for 1minute




Operating Temperature : -40°C to +105°C

► Terminated with 1.27mm pitch flat ribbon cable.

► Mating Suggestion: TC-D01 series.



POSITION	A	B	C	D	E	F
06	31.88	23.52	13.22	5.08	16.34	2.5
08	34.42	26.06	15.76	7.62	18.88	2.5
10	36.96	28.60	18.30	10.16	21.42	4.5
14	42.04	33.68	23.38	15.24	26.50	4.5
16	44.58	36.22	25.92	17.78	29.04	4.5
20	49.66	41.30	31.00	22.86	34.12	4.5
24	54.74	46.38	36.08	27.94	39.20	4.5
26	57.28	48.92	38.62	30.48	41.74	4.5
30	62.36	54.00	43.70	35.56	46.82	4.5
34	67.44	59.08	48.78	40.64	51.90	4.5
40	75.06	66.70	56.40	48.26	59.52	4.5
50	87.76	79.40	69.10	60.96	72.22	4.5
60	100.46	92.10	81.80	73.66	84.92	4.5
64	105.54	97.18	86.88	78.74	90.00	4.5



How to order: TC-D17 - **1** - **2** - **3** - **4** - **5** - G(RoHS)

Pitch 2,54mm x 2,54mm

1.NO. OF CONTACT	2.CONTACT MATERIAL	3.CONTACT PLATING	4.SPECIAL FUNCTION	5.INSULATOR COLOR
06 08 10 14 16 20 24 26 30 34 40 50 60 64	A: BRASS	T: TIN PLATED S: SELECTIVE G: GOLD FLASH A: 5u" INCH GOLD B: 10u" INCH GOLD C: 15u" INCH GOLD D: 30u" INCH GOLD	A: W EAR B: W/O EAR	2. GREY