

MK270

Wireless Keyboard and Mouse Combo

logitech®



The reliable wireless combo with a tiny Logitech plug-and-forget receiver.

PRODUCT BENEFITS

KEYBOARD

- Standard layout with full-size F-keys, number pad and arrow keys
- 19 mm pitch, 3.2 mm key travel
- Ultra-silent keys (<55 dB)
- Personalized comfort: 0° flat angle or 8° tilt angle
- Long life UV-coated, abrasion-resistant keys designed to last over 5 million keystrokes
- Spill-resistant up to 60 ml
- 128-bit AES keyboard encryption helps keep your information secure
- Bright LED status notification lights for Caps Lock
- 103 keys with integrated productivity shortcuts plus 8 separate hot keys for media controls

MOUSE

- Advanced optical tracking for smooth, responsive cursor control, easy text selection, and effortless scrolling
- Ambidextrous design for right and left-handed people
- The mouse features a built-in storage compartment for the receiver, so you can take your mouse wherever you use your computer

KEYBOARD & MOUSE

- 36-month keyboard and 12-month mouse battery life
- 3 year warranty
- Tiny USB receiver - you can plug it in once and forget about it. No software required
- Logitech® Advanced 2.4 GHz wireless connectivity for a reliable connection up to 10 metres away. Fast data transmission, virtually no delays or dropouts
- Auto-sleep and on/off switch

SPECIFICATIONS

Certification*

*Certified across multiple countries worldwide. List available upon request.

- CE
- FCC
- CB



Compatibility

Windows (XP, Vista, 7, 8, 10 and later) Chrome OS

Spill Resistant

YES

Warranty

3 years

Service Life

5 million key operations per key

Key Print (Durability)

Tampo + UV coating

Connectivity

USB Nano-receiver

Profile

Standard

Tilt Legs

YES

Tilt Angles

0° flat and 8° tilt

Keyboard Layout

Standard/Full size

Palm Rest

NO

Battery Life

24 months (KB)
12 months (M)

Hot Keys

8 Separate Hot Keys

Illuminated Keys

NO

Illuminated Caps Lock

YES

Illuminated Num Lock

NO

Integrated LCD

NO

Number Pad

YES

Number of Keys

103 + 8 hotkeys

Wireless Length

10 m (2,4 GHz)

Mouse Tracking

Optical

Mouse Scrolling

Ratchet Wheel

Ambidextrous Design

YES

DPI

1000

Product Weight

481 g (KB)
50 g (M)

Dimensions (W x D x H)

441.5 x 149 x 18 mm (KB)
60 x 39.1 x 99.1 mm (M)

Total Weight (with packaging)

866 g

Packaging Dimensions

524 x 159 x 50 mm

Storage Temperature

-40°C to 60°C

Operating Temperature

0°C to 40°C

Reliability

MTTF* > 150'000 hours
*Mean Time To Failure of electrical components

Layout

US INT'L, FRA, DEU, ITA, ESP, RUS,
ARA, ELL, HEB, UK, NLB, TUR,
HUN, CZE, CH, PAN-NORDIC

Packaging Unit

Master package: 6
Pallet: 60

Colours

Black

Key Technology

Plunger

Operating Instructions

Detailed instructions included



WORLD LEADER IN
MICE AND KEYBOARDS