

HDMI to VGA Video Adapter Converter with Audio - HD to VGA Monitor 1080p

StarTech ID: HDMI2VGA



The HDMI2VGA HDMI® to VGA converter converts digital HDMI or DVI video signals to analog VGA, taking the input resolution from your device and converting it into an analog signal at the same resolution.

The converter also separates the audio stream from the HDMI signal (HDMI LPCM 2-Channel) and converts it to analog stereo audio that can be used with the VGA display.

With support for resolutions of up to 1080p, the HDMI2VGA converter is a perfect solution for connecting video cards (desktop or laptop) or consumer electronics devices such as game consoles or home theater receivers that offer an HDMI output to a VGA display.

The HDMI2VGA adapter/converter is simple to use, with no complicated settings, and is backed by a 2-year warranty and free, lifetime technical support.

Applications

- Convert an HDMI® signal from a Blu-Ray player, PS3, or other HDMI-enabled source to work with an analog VGA display
- Convert a DVI or HDMI signal from a desktop or notebook video card to work with an analog VGA display / projector

Features

- Supports VGA and Component (YPbPr) output conversion
- Compliant with HDCP 1.1, and DVI
- Built-in EDID
- Audio video are separated on output

Technical Specifications

| | |
|---------------------------|---|
| Warranty | 2 Years |
| Audio | Yes |
| Converter Type | Format Converter |
| Audio Specifications | HDMI® LPCM 2-channel Input |
| Supported Resolutions | PC: 1920x1200, 1600x1200, 1680x1050, 1440x900, 1280x1024, 1280x800, 1152x864, 1024x768, 800x600, 640x480 |
| Connector A | HD: 1080p/1080i (50, 60Hz), 720p (50, 60Hz), 576i/576p (50Hz), 480i/480p (60Hz) 1 - HDMI (19 pin) Female Input |
| Connector B | 1 - 3.5 mm Mini-Jack (3 Position) Female Output |
| Connector B | 1 - VGA (15 pin; High Density D-Sub) Female Output |
| Note | PC resolutions below 1280x1024 may support multiple refresh rates; 60Hz supported across all |
| LED Indicators | 1 - Power (Red) |
| Center Tip Polarity | Positive |
| Input Current | 0.3A |
| Input Voltage | 100 ~ 240 AC |
| Output Current | 1.2A |
| Output Voltage | 5 DC |
| Plug Type | N |
| Power Source | AC Adapter Included |
| Humidity | 0~60% RH |
| Operating Temperature | 0°C to 40°C (32°F to 104°F) |
| Storage Temperature | -10°C to 60°C (14°F to 140°F) |
| Color | Black |
| Product Height | 3.6 in [92 mm] |
| Product Length | 3 in [76 mm] |
| Product Weight | 6.1 oz [172 g] |
| Product Width | 3 in [76 mm] |
| Shipping (Package) Weight | 18.4 oz [520 g] |
| Included in Package | 1 - HDMI to VGA Converter w/ Audio |
| Included in Package | 1 - VGA to Component Breakout Cable |

Included in Package 1 - Universal Power Adapter (US/UK/EU/AUS)

Included in Package 1 - Instruction Manual

Certifications, Reports and Compatibility

