

S-Video / Composite to USB Video Capture Cable w/ TWAIN and Mac Support

StarTech ID: SVID2USB23



The SVID2USB23 USB 2.0 S-Video & Composite Video Capture Cable offers an easy to use analog video capture solution, enabling you to grab video from an S-Video or Composite video source, as well as the accompanying 2-channel RCA audio, to your Mac® or Windows® computer.

The cable connects to your desktop or laptop computer through USB 2.0, and is compact enough to fit in the palm of your hand, providing a conveniently portable video capture solution that's more than suitable for use with laptops and desktop computers alike.

An easy-to-use device for recording analog video to your computer from external sources, such as a VCR or camcorder the SVID2USB23 offers the perfect solution for Betamax or VHS video capture, with real-time MPEG-1, MPEG-2, and MPEG-4 encoding, as well as TWAIN support, to ensure compatibility with a wide range of systems and software.

This analog video capture cable supports a broad range of operating systems, delivering seamless analog video capture for Mac® computers (OS 10.X), and Windows® PCs (Windows® 7, Windows® 2000/XP(32/64-bit)/Vista(32/64-bit)).

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Convert VHS home movies to digital format - Connect your VCR, camcorder, or any other analog video source to your Mac or PC and capture your audio/video in MPEG 1/2/4 format
- Import recorded videos onto your Mac® or Windows® computer for editing, and make your own compilation

Features

- Works with Mac® or Windows® computers
- Choose from MPEG-1, MPEG-2, or MPEG-4 video encoding
- Features TWAIN support for use with various software titles
- Supports NTSC, PAL, and SECAM video capture
- Up to 30 fps analog video capture capability at maximum resolution of 720x480(NTSC) / 720x576(PAL)
- Plug and Play device installation, requires no power adapter
- Snapshot function allows you to capture still images from video
- Small and lightweight design offers convenient portability for on-the-go applications

Technical Specifications

Warranty	2 Years
Audio	Yes
Chipset ID	eMPIA EM2861
Converter Type	Format Converter
Industry Standards	NTSC, PAL, SECAM Video Encoding: MPEG 1, MPEG 2, and MPEG 4.
Maximum Analog Resolutions	720x480(NTSC) / 720x576(PAL)
Maximum Data Transfer Rate	480Mbps
Connector A	1 - USB A (4 pin) Male Output
Connector B	1 - Composite Video (1 x RCA) Female Input
Connector B	1 - Stereo Audio (2 x RCA) Female Input
Connector B	1 - S-Video (4 pin; Mini-DIN) Female Input
OS Compatibility	Windows® 10 (32/64bit), 8/8.1 (32/64bit), 7 (32/64bit), Vista(32/64), XP(32/64), 2000 (Aero 3D interface supported) Apple® OSX Mavericks (10.9) Mountain Lion (10.8), Lion (10.7), Snow Leopard (10.6)
Humidity	5~85% RH Non-condensing
Operating Temperature	0°C to 50°C (32°F to 122°F)
Storage Temperature	-20°C to 60°C (-4°F to 140°F)
Color	Black
Enclosure Type	Plastic
Product Height	0.6 in [14 mm]
Product Length	3.1 in [80 mm]
Product Weight	2.5 oz [70 g]
Product Width	1.3 in [34 mm]
Shipping (Package) Weight	0.4 lb [0.2 kg]
Included in Package	1 - USB Video Capture Cable
Included in Package	1 - Software CD
Included in Package	1 - Driver CD
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

