

### 3 ft Mini DisplayPort to DVI Active Adapter Converter Cable – mDP to DVI 2560x1600 – Black

StarTech ID: MDP2DVIMM3BS



The MDP2DVIMM3BS 3ft active Mini DisplayPort to DVI adapter cable lets you directly connect your Mini DP video source (Laptop, Macbook®, Ultrabook™ etc.) directly to a nearby DVI monitor or projector, saving the expense of additional adapters while eliminating the clutter of excess cable.

For guaranteed compatibility with virtually any Mini DisplayPort output the active Mini DP to DVI adapter supports multimode (DP++) as well as single-mode DisplayPort signals. Unlike passive adapters, this ensures the MDP2DVIMM3BS can be used with graphics cards that are not capable of outputting multimode DP++ signals, such as ATI® Eyefinity cards.

Compatible with Intel® Thunderbolt™, when connected directly to a supporting DisplayPort over Thunderbolt™ I/O port, the adapter supports resolutions up to 2560x1600.

The MDP2DVIMM3BS is backed by a 2-year StarTech.com warranty and free lifetime technical support.

#### Applications

- Use with single-mode Mini DisplayPort video outputs that are not capable of outputting multimode DP++ signals, such as ATI® Eyefinity video cards
- Connect your DVI display device (monitor, projector) directly to a Mini DisplayPort output device
- Ideal for using your DVI monitor as a secondary display

## Features

- Active Mini DisplayPort to DVI conversion
- 1x Male DisplayPort connector, 1x Male DVI connector
- Compatible with Intel® Thunderbolt™ devices that are capable of outputting a DisplayPort signal
- Supports resolutions up to 2560x1600 and HDTV resolutions up to 1080p
- Plug-and-play Installation

## Technical Specifications

Warranty	2 Years
Adapter Style	Cable Adapter
Audio	No
Chipset ID	PS171A
Converter Type	Active
Maximum Cable Length	3 ft [0.9 m]
Maximum Digital Resolutions	2560x1600 (Dual link)
Supported Resolutions	2560x1600 1920x1200 1920x1080
Wide Screen Supported	Yes
Connector A	1 - Mini-DisplayPort (20 pin) Male
Connector B	1 - DVI-D (25 pin) Male
Humidity	40%-85%RH
Operating Temperature	0°C to 60°C (32°F to 140°F)
Storage Temperature	-10°C to 70°C (14°F to 158°F)
Cable Length	3 ft [0.9 m]
Color	Black
Product Height	0.6 in [15 mm]
Product Length	36.2 in [920 mm]
Product Weight	3.3 oz [93.2 g]
Product Width	1.6 in [40 mm]
Shipping (Package) Weight	3 oz [84 g]
Included in Package	1 - Active DisplayPort to DVI Adapter

Certifications, Reports and Compatibility

