

## 6 ft Mini DisplayPort to DVI Cable - M/M

StarTech ID: MDP2DVIMM6



The MDP2DVIMM6 6-foot Mini DisplayPort to DVI Cable is a cost-effective Mini DisplayPort to DVI link that lets you connect a DVI monitor to a PC or Mac® with a Mini DisplayPort output - saving the expense of upgrading the monitor for compatibility. This all-in-one, easy to use Mini DisplayPort/DVI cable requires no additional converters or adapters, and no driver or software installation.

Compatible with Intel® Thunderbolt™, when connected directly to a supporting DisplayPort over Thunderbolt™ I/O port.

MDP2DVIMM6 is a passive adapter that requires a DP++ port (DisplayPort++), meaning that DVI and HDMI signals can also be passed through the port.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Applications

- Keep your existing DVI display with our Mini DisplayPort to DVI video converter cables
- Use a DVI monitor with DisplayPort equipped MacBook's and iMac's with Mini DisplayPort video output

## Features

- All-in-one cable design
- Supports resolutions up to 1920x1200 and HDTV resolutions up to 1080p
- No software or additional drivers required
- Compatible with Intel® Thunderbolt™

## Technical Specifications

Warranty	2 Years
Adapter Style	Cable Adapter
Audio	No
Converter Type	Passive
Maximum Cable Length	6 ft [1.8 m]
Maximum Digital Resolutions	1920x1200 / 1080p
Connector A	1 - Mini-DisplayPort (20 pin) Male
Connector B	1 - DVI-D (25 pin) Male
System and Cable Requirements	DP++ (DisplayPort++) port required on video card or video source for DVI and HDMI signal pass-through.
Humidity	20~80% RH
Operating Temperature	5°C to 35°C (41°F to 95°F)
Storage Temperature	0°C to 70°C (32°F to 158°F)
Cable Length	6 ft [1.8 m]
Color	Black
Product Length	6 ft [1.8 m]
Product Weight	3.2 oz [90 g]
Shipping (Package) Weight	3.2 oz [90 g]
Included in Package	1 - 6 ft Mini DisplayPort to DVI Cable - M/M

Certifications, Reports and Compatibility

