

Mini DisplayPort to VGA Adapter Cable with Audio - 10 ft (3m)

StarTech ID: MDP2VGAAMM3M



Now you can organize your workspace with less mess than ever before.

This unique 10-foot Mini DisplayPort™ to VGA adapter cable features a built-in audio port, which enables you to connect a VGA monitor as well as speakers to your Mini DisplayPort (mDP) equipped desktop computer.



Create a clutter-free environment

Remove the cable clutter from your desk. With the built-in audio port you no longer need to run a separate audio cable from your monitor or speakers directly to your desktop or laptop computer. Simply plug the audio cable from your speakers into the adapter cable for a simple and tidy solution.

In order to use the audio function of the adapter, it needs to be powered through USB. Simply connect a Micro-USB cable into the adapter from your computer, monitor or USB grommet in order to provide the necessary power.

Substitute for a damaged audio port

The adapter guarantees you always have all of the connections you need. If the audio port on your computer is damaged or blocked, this adapter cable ensures you still have sound available for watching video presentations, listening to music while you work or chatting with your colleagues over Skype™.

The adapter cable is compatible with Intel® Thunderbolt™, when connected directly to a supporting DisplayPort over Thunderbolt™ I/O port, and supports resolutions up to 1920x1200 (WUXGA).

The MDP2VGAAMM3M is backed by a 2-year StarTech.com warranty and free lifetime technical support.

Applications

- Connect your speakers and a VGA monitor to your Mini DisplayPort equipped computer with the cables hidden and out of the way
- Use in your boardroom or office workstations for installations requiring 10 feet of cable

Features

- Create a clutter-free work environment by placing your audio and video cables neatly behind your monitor
- Substitute a damaged or blocked audio port by connecting your speakers to your computer directly through the adapter
- Provide crystal-clear picture quality with support for high-definition video resolutions up to 1920x1200 or 1080p

Technical Specifications

Warranty	2 Years
Adapter Style	Cable Adapter
Audio	Yes
Converter Type	Active
Audio Specifications	2-channel stereo (3.5mm)
Maximum Analog Resolutions	1920x1200 / 1080p (output)
Maximum Digital Resolutions	1920x1200 / 1080p (input)
Wide Screen Supported	Yes
Connector A	1 - Mini-DisplayPort (20 pin) Male
Connector B	1 - VGA (15 pin; High Density D-Sub) Male
Connector B	1 - 3.5 mm Mini-Jack (3 Position) Female
Connector Type(s)	1 - USB Micro-B (5 pin) Female
Power Source	USB-Powered
Humidity	40%~50%RH
Operating Temperature	0°C to 70°C (32°F to 158°F)
Storage Temperature	-10°C to 55°C (14°F to 131°F)
Cable Length	9.8 ft [3 m]
Color	Black
Product Height	0.6 in [16.5 mm]
Product Length	9.8 ft [3 m]
Product Weight	5.2 oz [146 g]
Product Width	1.6 in [39.7 mm]
Shipping (Package) Weight	5.9 oz [168 g]
Included in Package	1 - 3m Mini DisplayPort to VGA adapter cable with audio
Included in Package	1 - 0.5m Micro USB cable

Certifications, Reports and Compatibility

