

Mini DisplayPort to VGA Video Adapter Converter - White

StarTech ID: MDP2VGAW



The MDP2VGAW Mini-DisplayPort® to VGA Adapter (White) offers an easy-to-use VGA/Mini-DisplayPort link that enables you to connect a VGA computer monitor to a device with a Mini-DisplayPort output (such as a laptop video out port) or video card.

The adapter cable is compatible with Intel® Thunderbolt™, when connected directly to a supporting DisplayPort over Thunderbolt I/O port. Plus, because the converter cable supports video resolutions up to 1920x1200 you can convert a Mini DisplayPort video source to a VGA monitor without sacrificing video quality.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Ideal for digital entertainment centers, home offices, business conference rooms and trade show displays
- Keep your existing VGA monitor to be used with your new Mini-DisplayPort device
- Ideal for using your VGA monitor as a secondary display

Features

- Supports PC resolutions up to 1920x1200 and HDTV resolutions up to 1080p
- Easy to use adapter, no software required
- Compatible with Intel® Thunderbolt™

Technical Specifications

Warranty	2 Years
Adapter Style	Adapter
Audio	No
Converter Type	Active
Industry Standards	DisplayPort 1.1a
Maximum Analog Resolutions	1920x1200
Connector A	1 - Mini-DisplayPort (20 pin) Male
Connector B	1 - VGA (15 pin; High Density D-Sub) Female
Humidity	40~85% RH
Operating Temperature	0°C to 60°C (32°F to 140°F)
Storage Temperature	-10°C to 70°C (14°F to 158°F)
Cable Length	4.7 in [120 mm]
Color	White
Enclosure Type	Plastic
Product Height	0.6 in [15 mm]
Product Length	7.1 in [180 mm]
Product Weight	1.1 oz [31 g]
Product Width	1.8 in [45 mm]
Shipping (Package) Weight	1.5 oz [42 g]
Included in Package	1 - Mini DisplayPort® to VGA adapter

Certifications, Reports and Compatibility

