

Travel A/V Adapter: 3-in-1 Mini DisplayPort to VGA DVI or HDMI Converter - White

StarTech ID: MDP2VGDVHDW



The MDP2VGDVHDW Mini DisplayPort to VGA, DVI or HDMI converter offers a three-in-one solution for connecting an mDP source such as a Thunderbolt™-enabled MacBook Pro® / MacBook Air® to a VGA, DVI, or HDMI Display. Ensuring compatibility with almost any display, television or projector, this compact and lightweight adapter offers the ideal plug-and-play solution for travel, or BYOD (Bring Your Own Device) applications around the office.

You can walk into any boardroom and be ready to connect, even if you don't know what connection ports are available. The MDP2VGDVHDW maximizes the audio/video connectivity of your MacBook® by offering three different output ports, in a single compact adapter.



The three-in-one converter is compatible with Intel® Thunderbolt, when connected directly to a supporting DisplayPort over Thunderbolt I/O port. Plus, because the converter cable supports video resolutions up to 1920x1200/1080p you can convert a Mini DisplayPort video source to VGA, HDMI, or DVI without sacrificing video quality.

The Mini DisplayPort converter requires no power adapter and maximizes portability by easily travelling in your laptop bag with a small footprint and lightweight design.



The MDP2VGDVHDW features a sleek white design that looks great next to your MacBook® Pro or MacBook Air®, and is backed by a 2-year StarTech.com warranty and free lifetime technical support.

Applications

- Keep the adapter with you while traveling, to connect to virtually any display you come across
- Connect your BYOD laptop/Ultrabook to a provided HDMI, DVI, or VGA display at work
- Connect a DVI, VGA, or HDMI display to your Mini DisplayPort laptop, to use as a secondary monitor

Features

- Three-in-one adapter - mDP to: VGA, DVI, HDMI
- Support for video resolution up to 1920x1200/1080p
- Plug-and-play installation
- Compatible with Intel® Thunderbolt™ devices that are capable of outputting a DisplayPort signal
- Small footprint
- Portable, lightweight construction
- Sleek White Design

Technical Specifications

Warranty	2 Years
Adapter Style	Adapter
Audio	Yes
Converter Type	Travel A/V Adapters
Output Signal	DisplayPort
Output Signal	HDMI
Audio Specifications	5.1 Surround Sound (Video source and destination dependant)
Maximum Analog Resolutions	1920x1200/1080p
Maximum Digital Resolutions	1920x1200/1080p
Wide Screen Supported	Yes
Connector A	1 - Mini-DisplayPort (20 pin) Male
Connector B	1 - HDMI (19 pin) Female
Connector B	1 - VGA (15 pin; High Density D-Sub) Female
Connector B	1 - DVI-D (25 pin) Female
Note	Only one video output is supported on the video adapter at a time. If multiple connections are made, only one of the outputs will function.
Humidity	10~85% RH
Operating Temperature	0°C to 70°C (32°F to 158°F)
Storage Temperature	-10°C to 80°C (14°F to 176°F)
Product Height	0.6 in [15 mm]
Product Length	10.6 in [270 mm]
Product Weight	1.8 oz [51 g]
Product Width	1.8 in [45 mm]
Shipping (Package) Weight	0.4 oz [10 g]
Included in Package	1 - Mini DisplayPort to HDMI/VGA/DVI Adapter
Included in Package	1 - Installation Guide

Certifications, Reports and Compatibility

