

Computer power cord - C13 to C20, 14 AWG, 3 ft

StarTech ID: *PXTC13C20143*



This C13 to C20 power cord from StarTech.com features 14 AWG wire that's suitable for high-power connections, making it perfect for server application and connecting to a Power Distribution Unit (PDU).

Expertly designed and constructed of high-quality materials, the PXTC13C20143 power cord is backed by our lifetime warranty.

Applications

- Connect your server to a PDU
- Extend the connection between your server and PDU by up to 3 feet

Features

- Rated to carry 125V at 15A
- 14 AWG wire
- UL, RoHS compliant

Technical Specifications

Warranty	Lifetime
Cable Jacket Type	PVC - Polyvinyl Chloride
Cable Type	SJT
Number of Conductors	3
Connector A	1 - IEC 60320 C13 Power
Connector B	1 - IEC 60320 C20 Power
Input Current	15 A
Input Voltage	125 AC
Cable Length	3 ft [0.9 m]
Color	Black
Product Length	3 ft [0.9 m]
Product Weight	8 oz [228 g]
Wire Gauge	14 AWG
Package Quantity	1
Shipping (Package) Weight	8.3 oz [234 g]
Included in Package	1 - 3 ft 14 AWG Computer Power Cord - C13 to C20

Certifications, Reports and Compatibility

