

**10 ft Black USB 2.0 Extension Cable A to A - M/F**

*StarTech ID: USBEXTAA10BK*



The USBEXTAA10BK 10-foot USB Extension Cable (A-A) features 1 USB A male connector and 1 USB A female connector, extending the connection between USB 2.0 devices by up to 10 feet - an ideal solution for better placement of peripheral devices, or adding flexibility to existing USB ports.

This high quality USB extension cable is fully rated for use with USB 1.1 and USB 2.0 devices, and is backed by StarTech.com's Lifetime Warranty.

**Applications**

- Extend your USB connection to connect a USB printer or any USB peripheral device to a PC or Mac at high-performance data transfer speed

**Features**

- Designed and constructed to USB 2.0 specifications
- Molded strain relief
- Supports data transfer rates up to 480 Mbps

## Technical Specifications

Warranty	Lifetime
Cable Jacket Type	PVC - Polyvinyl Chloride
Cable Shield Type	Aluminum-Mylar Foil with Braid
Connector Plating	Nickel
Type and Rate	USB 2.0 - 480 Mbit/s
Connector A	1 - USB A (4 pin) Male
Connector B	1 - USB A (4 pin) Female
Cable Length	10 ft [3 m]
Color	Black
Product Weight	0.2 lb [0.1 kg]
Wire Gauge	24/28 AWG
Shipping (Package) Weight	0.2 lb [0.1 kg]
Included in Package	1 - 10 ft Black USB 2.0 Extension Cable A to A - M/F

## Certifications, Reports and Compatibility

