

## 1m 3.5mm 4 Position TRRS Headset Extension Cable - M/F

StarTech ID: MUHSMF1M



The MUHSMF1M 4-Pole 3.5mm headset extension cable (1m) features a 3.5mm (1/8" TRRS) audio connector on one end and a 3.5mm (1/8" TRRS) audio connector on the other, making it easy to extend the reach between your hands-free headset or headphones, and your iPhone®, mobile phone or laptop computer.

To ensure long-lasting performance, this high quality 3.5mm audio extension cable features molded PVC strain relief at each of the 1/8" TRRS connectors, which prevents the cable termination points from bending at sharp angles, in turn reducing the risk of cable damage.

### Please note:

To ensure proper hardware detection, we recommend that the external headset be plugged into the adapter first, before the adapter is connected to the computer or mobile device.

Also, in some circumstances, when an extension cable is used with an in-line remote control equipped headset, the remote control functions may not operate properly. This is due to the sensitivity of the remote control circuitry and does not indicate any defect in the cable.

## **Applications**

- Extend the reach between your hands-free headset and an iPhone® or other mobile phone
- Add connection distance between your headset and your laptop or desktop computer audio port



#### **Features**

- 4-pole 3.5mm connectors with molded PVC strain relief
- 90% Spiral Wrapped Connector provides shielding against EMI and RFI interference

## **Technical Specifications**

Warranty Lifetime

Cable Jacket Type PVC - Polyvinyl Chloride

Connector Plating Nickel

Connector A 1 - 3.5 mm Mini-Jack (4 Position) Male
Connector B 1 - 3.5 mm Mini-Jack (4 Position) Female

Cable Length 3.3 ft [1 m]

Color Black

Product Length 3.3 ft [1 m]
Product Weight 0.7 oz [20 g]
Wire Gauge 28 AWG

Package Quantity 1

Shipping (Package) Weight 0.1 lb [0 kg]

Included in Package 1 - 1m 3.5mm 4 Position Headset Extension Cable - M/F

# **Certifications, Reports and Compatibility**

