

## 1 Port PCI Express PCIe Gigabit NIC Server Adapter Network Card - Low Profile

StarTech ID: ST1000SPEX2L



The ST1000SPEX2L Low-Profile PCIe Gigabit Network Card adds a 10/100/1000 Mbps compatible RJ45 Ethernet port to a PCI Express-enabled client, server or workstation, providing a convenient addition or replacement networking interface.

Compliant with IEEE 802.3/u/ab standards, and with support for 9K Jumbo Frames, VLAN tagging and Wake on LAN (WOL), this versatile Gigabit NIC/Server Adapter offers effective network performance.

The card comes pre-configured with a low-profile/half-height installation bracket and includes a standard profile bracket for installation in a wide range of computer/server chassis, regardless of form factor.

Backed by a 2-year StarTech.com warranty and free lifetime technical support.

### Applications

- Upgrade from 10/100 Ethernet capability to Gigabit capability
- Add an Ethernet port to a workstation or server computer, for redundancy or bridging
- Add networking capabilities to an old system with no Ethernet port

## Features

- A single 10/100/1000Mbps compatible RJ45 Ethernet port
- Gigabit detection and Link/Activity LED indicators
- Fully Compliant with IEEE 802.3, IEEE 802.3u, IEEE 802.3x and IEEE 802.3ab standards
- Supports IEEE 802.1Q VLAN tagging, IEEE 802.1P Layer 2 Priority Encoding and IEEE 802.3x Full Duplex Flow Control
- Jumbo frame support
- Full and half duplex support
- Supports Wake-on-LAN function
- Crossover Detection & Auto-Correction (Auto MDI/MDI-X)

Technical Specifications

Warranty	2 Years
Bus Type	PCI Express
Card Type	Low Profile (SP bracket incl.)
Chipset ID	Realtek RTL8111E
Industry Standards	IEEE 802.3, IEEE 802.3u, IEEE 802.3x, IEEE 802.3ab
Interface	RJ45 (Gigabit Ethernet)
Ports	1
Auto MDIX	Yes
Compatible Networks	10/100/1000 Mbps
Full Duplex Support	Yes
Jumbo Frame Support	9K max.
Maximum Data Transfer Rate	1000 Mbps
Supported Protocols	CSMA/CD
Connector Type(s)	1 - PCI Express x1
External Ports	1 - RJ-45
OS Compatibility	Windows® 2000, XP, Vista, 7, 8, 8.1, 10 Windows Server® 2003, 2008 R2, 2012, 2012 R2 Mac OS X® 10.6 to 10.9 Linux 2.4.x to 4.4.x <i>LTS Versions Only</i>
System and Cable Requirements	Available PCI Express expansion card slot
LED Indicators	1 - Gigabit Detect (Yellow)
LED Indicators	1 - Link/Activity (Green)
Humidity	10% ~ 90% RH
Operating Temperature	0°C to 70°C (32°F to 158°F)
Storage Temperature	0°C to 100°C (32°F to 212°F)
Product Height	1.9 in [49 mm]
Product Length	2.8 in [70 mm]
Product Weight	1.1 oz [30 g]
Product Width	0.7 in [18 mm]
Shipping (Package) Weight	4.5 oz [127 g]
Included in Package	1 - Gigabit Ethernet PCI Express Card
Included in Package	1 - Standard Profile Bracket
Included in Package	1 - Driver CD
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

