

USB 2.0 to 10/100 Mbps Ethernet Network Adapter Dongle

StarTech ID: USB2100



The USB2100 USB 2.0 to 10/100 Mbps Network Adapter lets you add a Fast Ethernet port to your laptop or desktop computer through USB.

This compact USB network adapter offers a dongle design with a built-in cable to avoid cramped connections, making it a perfect solution for adding wired Ethernet connectivity to your desktop without opening the case, or to replace a failed onboard network adapter on your laptop system.

Providing half or full-duplex operation, this USB 2.0 Ethernet adapter supports data transfer rates of up to 200 Mbps. The adapter also supports features such as Wake-on-LAN (WoL) and VLAN tagging for added flexibility.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Add a 10/100 Mbps Ethernet port to any desktop or laptop without opening the case
- Replacement for a failed onboard Ethernet port on a desktop or laptop

Features

- 10/100 Mbps Ethernet through USB 2.0
- IEEE 802.3i and 802.3u (10BASE-T, 100BASE-TX) compatible
- Supports half / full-duplex operation
- Crossover Detection & Auto-Correction (Auto MDIX)
- IEEE 802.1Q VLAN Tagging support
- Dongle with integrated USB cable

Technical Specifications

Warranty	2 Years
Bus Type	USB 2.0
Chipset ID	ASIX - AX88772C
Industry Standards	IEEE802.3i, IEEE 802.3u
Interface	RJ45 (10/100 Ethernet)
Ports	1
USB Pass-Through	No
Auto MDIX	Yes
Compatible Networks	10/100 Mbps
Full Duplex Support	Yes
Max Distance	100 m / 330 ft
Maximum Data Transfer Rate	200 Mbps (Ethernet - Full-Duplex)
Type and Rate	USB 2.0 - 480 Mbit/s
Connector Type(s)	1 - USB A (4 pin) Male
Connector Type(s)	1 - RJ-45 Female
OS Compatibility	Windows® XP, Vista, 7, 8, 8.1, 10 Windows Server® 2003, 2008 R2, 2012 Mac OS X® 10.6 to 10.11 Google Chrome OS™ Linux 2.6.x to 4.4.x <i>LTS Versions only</i>
System and Cable Requirements	Available USB port
LED Indicators	1 - Link
LED Indicators	1 - Activity
Power Source	USB-Powered
Humidity	10~90% RH
Operating Temperature	10°C to 40°C (50°F to 114°F)
Storage Temperature	-20°C to 70°C (-4°F to 158°F)
Cable Length	5.9 in [150 mm]
Color	Black
Enclosure Type	Plastic
Form Factor	Attached Cable
Product Height	0.6 in [14 mm]
Product Length	2.6 in [65 mm]
Product Weight	0.8 oz [22 g]

Product Width	0.8 in [20 mm]
Shipping (Package) Weight	4.6 oz [130 g]
Included in Package	1 - USB 2.0 Fast Ethernet Adapter
Included in Package	1 - Driver CD
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

