

USB 3.0 Front Panel 4 Port Hub – 3.5in or 5.25in Bay

StarTech ID: 35BAYUSB3S4



The 35BAYUSB3S4 3.5-inch Front Bay to 4-Port USB 3.0 Panel Hub turns any available 3.5-inch computer case front bay into a 4-Port USB 3.0 hub.

Using only a single USB connection, this front panel hub adds four easily accessible USB ports to the front of your computer case through a 3.5-inch bay, or through a 5.25-inch bay using the optional [Front Bay Bracket Adapter](#) (BRACKETFDBK) accessory. Each of the added ports is compliant with the USB 3.0 standard which supports up to 5 Gbps of bandwidth (10x faster than the USB 2.0 standard) and up to 900mA of power.

Accessorize with the PEXUSB3S11 PCI Express card to provide an internal USB 3.0 port, so as to keep the external ports free for external devices. Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Expand your system's USB 3.0 capabilities with additional ports for connecting high speed external storage devices
- Add easier to access USB ports to the front of a computer system instead of the rear
- Make use of an internal USB port and unused 3.5" front bay to increase the system's expandability

Features

- Four front accessible USB type-A ports
- Fits into any 3.5" computer case front bay
- SuperSpeed USB 3.0 compliant, supporting data transfer rates up to 5 Gbps
- Backward compatible with USB 2.0 and USB 1.0/1.1 specifications and devices
- Provides up to 900mA of power per port
- USB Link LED indicator for each port

Technical Specifications

Warranty	2 Years
Chipset ID	VLI - VL810
Fast-Charge Port(s)	No
Interface	USB 3.0
Ports	4
USB-C Device Port(s)	No
USB-C Host Connection	No
Type and Rate	USB 3.0 - 5 Gbit/s
External Ports	4 - USB 3.0 A (9 pin; SuperSpeed) Female
Internal Ports	1 - SATA Power (15 pin) Plug
Internal Ports	1 - USB 3.0 B (9 pin; SuperSpeed) Female
OS Compatibility	OS Independent; No additional drivers or software required
System and Cable Requirements	Available 3.5 inch front bay
System and Cable Requirements	Available USB 3.0 type A port
LED Indicators	4 - USB Device Link (Green)
Power Source	USB-Powered
Humidity	20% ~ 80% RH
Operating Temperature	5°C to 50°C (41°F to 122°F)
Storage Temperature	-25°C to 70°C (-13°F to 158°F)
Color	Black
Enclosure Type	Plastic
Form Factor	Drive Bay
Product Height	1 in [25 mm]
Product Length	4.7 in [120 mm]
Product Weight	3.5 oz [100 g]
Product Width	3.9 in [100 mm]
Shipping (Package) Weight	7.6 oz [214 g]
Included in Package	1 - 3.5" Front Panel
Included in Package	1 - USB 3.0 Cable
Included in Package	1 - Mounting Screw Kit
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

