

6 Port USB 3.0 / USB 2.0 Combo Hub with 2A Charging Port – 2x USB 3.0 & 4x USB 2.0

StarTech ID: ST7320USBC



The ST7320USBC 6-Port USB 3.0/2.0 Combo Hub features a special high-output dedicated charging port which enables you to charge USB devices by providing up to 2A of power, or it can add 2x USB 3.0 and 4x USB 2.0 ports to a computer through a single USB 3.0 host connection.

The hub includes an external power adapter, which when connected enables charging some portable electronic devices (e.g. an iPhone® or other Smartphone), even without a USB connection to a host computer.

Offering a unique design that features USB ports along 3 sides of the hub, as well as a combination of USB 2.0 and 3.0 ports, this versatile and flexible USB hub is ideal for both laptop and desktop computers.

The ST7320USBC USB 3.0/2.0 hub is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Add multiple USB 3.0 and USB 2.0 to a computer system to support more device connections
- Charge a Smartphone
- Charging high-powered portable devices (such as tablets) which require special high output USB ports for charging
- Make USB ports that are hard to access more accessible, by being positioning the hub in a convenient location (within cable reach)
- Extend the range of a USB device by having the hub act as a mid-point repeater

Features

- 2x USB 3.0 and 4x USB 2.0 ports that can be all accessed simultaneously
- 2 Amp high output USB Dedicated Charging Port (DCP)
- SuperSpeed USB 3.0 compliant host interface, with support for up to 5 Gbps of data bandwidth

Technical Specifications

Warranty	2 Years
Chipset ID	VLI - VL810
Fast-Charge Port(s)	Yes
Interface	USB 3.0
Ports	7
USB-C Device Port(s)	No
USB-C Host Connection	No
Type and Rate	USB 2.0 - 480 Mbit/s
Type and Rate	USB 3.0 - 4.8 Gbit/s
External Ports	1 - USB 3.0 B (9 pin; SuperSpeed) Female
External Ports	2 - USB 3.0 A (9 pin; SuperSpeed) Female
External Ports	4 - USB A (4 pin) Female
OS Compatibility	OS Independent
System and Cable Requirements	Available USB 3.0 or 2.0 port
LED Indicators	1 - Power
Input Current	0.6 A
Input Voltage	110 ~ 240 AC
Output Current	4 A
Output Voltage	5 DC
Plug Type	H
Power Source	AC Adapter Included
Humidity	5~90% RH
Operating Temperature	0°C to 85°C (32°F to 185°F)
Storage Temperature	-10°C to 95°C (14°F to 203°F)
Color	Black
Enclosure Type	Plastic
Form Factor	Desktop
Product Height	0.8 in [20 mm]
Product Length	3.9 in [99 mm]
Product Weight	2.7 oz [75.4 g]
Product Width	2.4 in [60 mm]
Package Quantity	1
Shipping (Package) Weight	17.6 oz [500 g]

Included in Package	1 - 6 Port USB Hub
Included in Package	1 - USB 3.0 Cable
Included in Package	3 - Universal Power Adapter (NA/EU/UK) and AU in Australia
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

