

CFast Card to SATA Adapter with 2.5" Housing

StarTech ID: CFAST2SAT25



Now you can use your CFast™ memory card like a standard 2.5" SATA solid-state drive. This unique adapter lets you access and recover data from a CFast card through SATA at faster data transfer speeds.

Turn CFast into SATA with ease

This CFast to SATA adapter creates a permanent conversion from CFast to SATA for use inside small form factor or embedded solutions. The drive frame and the connector on the adapter mimic the exact size and connector location of a 2.5" SATA hard drive.

Standard 2.5" housing allows the converted card to be installed into a laptop or other standard mounting bracket. Once the CFast card is mounted inside this adapter, you can use it just like a 2.5" SATA drive - in your laptop, docking station, enclosure or desktop computer.

Access your data faster with SATA performance

Transfer data from your CFast card to your PC through SATA, with file transfer speeds of up to 6 Gbps. You can offload data from your DSLR cameras and camcorders, or transfer graphic design files, videos and other files from your CFast card.

Faster file transfer speeds means you'll spend less time waiting for file transfers to complete. The actual speed will depend on the speed of the CFast media.

Engineered with a durable protective housing, the CFAST2SAT25 adapter is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Access and recover data from a CFAST card quickly through SATA
- Offload data from high-end digital cameras and camcorders, or to transfer graphic design files and videos

Features

- Make your CFast card work like a 2.5in SATA SSD
- Supports SATA III with data transfer speeds of up to 6 Gbps
- SATA and power combo connector (7 + 15 pin) - same as a 2.5" SATA hard drive
- Standard 2.5" housing allows the converted card to be installed into a laptop
- Durable protective housing
- OS independent, with no drivers or software installation required

Technical Specifications

Warranty	2 Years
Compatible Drive Types (Type and Rate)	CFast Type I, II
Number of Drives	1
Supported Drive Height(s)	3.3mm
Supported Drive Height(s)	5mm
Insertion Rating	10,000
Maximum Data Transfer Rate	6 Gbps
Memory Media Type	CFast (I/II Card)
MTBF	50,000
Type and Rate	SATA III (6 Gbps)
Drive Connectors	1 - CFast Data & Power Combo (7+17 pin) Plug
Host Connectors	1 - SATA Data & Power Combo (7+15 pin) Plug
OS Compatibility	OS independent; No software or drivers required
Humidity	5%~95% RH
Operating Temperature	0°C to 75°C (32°F to 167°F)
Storage Temperature	-40°C to 85°C (-40°F to 185°F)
Color	Black & Silver
Enclosure Type	Steel and Plastic
Product Height	0.4 in [9.9 mm]
Product Length	3.9 in [99 mm]
Product Weight	1.9 oz [54 g]
Product Width	2.7 in [69 mm]
Shipping (Package) Weight	0.2 lb [0.1 kg]
Included in Package	1 - CFast card to SATA converter
Included in Package	1 - Assembly screw kit
Included in Package	1 - Quick install guide

Certifications, Reports and Compatibility

