

USB 3.0 to eSATA HDD / SSD / ODD Adapter Cable - 3ft eSATA Hard Drive to USB 3.0 Adapter Cable - SATA 6 Gbps

StarTech ID: USB3S2ESATA3



The USB3S2ESATA3 USB 3.0 to eSATA drive cable lets you connect any external eSATA hard drive, solid state drive, or optical disc drive to your USB-enabled computer system -- a great solution for computers that don't natively support eSATA, such as MacBook® and Ultrabook™ computers.

To maximize performance and utilize the speed potential of your SATA 6 Gbps drives, the USB 3.0 to eSATA adapter is compatible with SATA revisions I/II/III and supports transfer speeds up to 5 Gbps through USB 3.0.

With support for Blu-ray/DVD/CD ATAPI / ODD drives and large capacity HDD / SSDs (tested up to 4TB) the USB to eSATA adapter cable is compatible with virtually any eSATA device, and can greatly increase the storage/backup capabilities of your computer.

The USB 3.0 to eSATA drive cable ensures a hassle-free connection with simple plug-and-play installation, plus the cable is the perfect length (1-meter, end-to-end) for easily accessing the rear panel USB ports on your computer.

The USB3S2ESATA3 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Connect an external eSATA drive to a computer system that only has USB
- Carry with your laptop and eSATA drive for an on the go storage solution
- Swap an eSATA drive between computers systems that do not have eSATA

Features

- Compatible with USB 3.0/2.0/1.1 (5 Gbps / 480 Mbps / 1.5 Mbps)
- eSATA interface compliant with SATA revision 3 and other SATA revisions, with supported data transfer rates up to 6 Gbps
- Supports hard drives (HDD), solid state drives (SSD) and optical disc drives (ODD)
- 1x eSATA connector, 1x USB 3.0 connector with integrated 1m (3.3ft) cable
- No driver or software installation required
- Plug-and-Play and Hot-Swap compatible

Technical Specifications

Warranty	2 Years
Bus Type	USB 3.0
Chipset ID	ASMedia - ASM1153E
Compatible Drive Types (Type and Rate)	SATA
Number of Drives	1
Hot Swap Capability	Yes
Max Drive Capacity	Currently tested with up to 4TB 7200 RPM hard drives
Maximum Data Transfer Rate	5 Gbps
Port Multiplier	No
Type and Rate	USB 3.0 - 5 Gbit/s
Type and Rate	SATA III (6 Gbps)
UASP Support	No
Drive Connectors	1 - eSATA (7 pin; Data) Female
Host Connectors	1 - USB Type-A (9 pin) USB 3.0 Male
OS Compatibility	OS independent; No software or drivers required
Humidity	40%-85%RH
Operating Temperature	0°C to 60°C (32°F to 140°F)
Storage Temperature	-10°C to 70°C (14°F to 158°F)
Product Height	0.4 in [10 mm]
Product Length	35.8 in [910 mm]
Product Weight	2.8 oz [80 g]
Product Width	0.9 in [24 mm]
Shipping (Package) Weight	2.8 oz [80 g]
Included in Package	1 - USB 3.0 to eSATA Adapter Cable
Included in Package	1 - Installation guide

Certifications, Reports and Compatibility

