

Cisco Compatible Gigabit Fiber SFP Transceiver Module SM LC w/ DDM – 20 km (Mini-GBIC)

StarTech ID: SFPG1320C



The SFPG1320C Cisco® Compatible Gigabit Fiber SFP Transceiver Module SM LC - 20 km (12.4 miles) is built to comply with MSA (Multi-Sourcing Agreement) standards to offer a cost-effective way to add, replace or upgrade a Single-Mode LC port on your Gigabit fiber networking equipment or fiber media converter.

Supporting data rates up to 1.25 Gbps as well as Digital Diagnostics Monitoring (DDM), this LC SFP/Mini-GBIC module can be installed into any fiber networking device with an MSA or Cisco compliant SFP port. Delivering both convenience and scalability, this fiber transceiver is fully hot-pluggable, which enables you to install the module without interrupting network traffic or requiring a device reboot.

This 1310nm single-mode SFP module is compatible with Cisco equipment.

Backed by a StarTech.com lifetime warranty and free lifetime technical support.

Applications

- Replacing defective or damaged SFPs in MSA compliant or Cisco equipment
- Expand your network to remote segments

Features

- Data rates up to 1.25 Gbps
- Supports distances up to 20 km (12.4 miles)
- Complies with SFP Multi-Source Agreements standards (MSA)
- Compatible with Cisco equipment
- LC Fiber connector
- Fully Hot Pluggable

Technical Specifications

Warranty	Lifetime
Industry Standards	IEEE 802.3z 1000BASE-LH
WDM	No
Compatible Networks	1000 Mbps (1 Gbps)
DDM	Yes
Fiber Operating Mode	Half/Full-Duplex
Fiber Type	Single Mode
Max Transfer Distance	20 km (12.4 mi)
Maximum Data Transfer Rate	1.25 Gbps
Wavelength	1310nm
Local Unit Connectors	1 - Fiber Optic LC Duplex Female
Note	For use in Gigabit fiber networking equipment and media converters
System and Cable Requirements	MSA or Cisco compliant SFP port
Humidity	30~70% RH
Operating Temperature	0°C to 70°C (32°F to 158°F)
Storage Temperature	-40°C to 85°C (-40°F to 185°F)
Product Height	0.4 in [10 mm]
Product Length	2.4 in [60 mm]
Product Weight	0.6 oz [17 g]
Product Width	0.5 in [12 mm]
Shipping (Package) Weight	1.7 oz [49 g]
Included in Package	1 - 1.25 Gbps Single Mode LC SFP

Certifications, Reports and Compatibility

