

10 ft USB to Parallel Printer Adapter - M/M

StarTech ID: ICUSB128410



The ICUSB128410 10 ft USB to Parallel Printer Adapter - M/M allows USB capable PCs to print to any standard parallel printer, converting a USB port into a Centronics (male) connector for direct connection to a parallel printer.

The USB interface provides a much faster data transfer rate than standard parallel ports, thereby reducing the time spent waiting for a print job or data transfer to be sent.

A portable, space-saving solution, the USB to Parallel Printer Adapter is self-powered and provides Plug and Play installation on Windows® based, USB-compliant computers.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Allows you to quickly add a parallel port to your Windows® computer

Features

- High speed bi-directional parallel port compliant to IEEE-1284 industry standard
- Low power consumption as it draws power from the USB connection
- Fully Plug & Play for easy installation
- No IRQ required for installation

Technical Specifications

Warranty	2 Years
Bus Type	USB 2.0
Chipset ID	Prolific - PL-2305
Interface	Parallel
Ports	1
Connector Type(s)	1 - Centronics (36 pin) Male
Connector Type(s)	1 - USB A (4 pin) Male
OS Compatibility	Windows® 98SE, ME, 2000, XP, Vista, 7, 8, 8.1, 10 Windows Server® 2000, 2003, 2008 R2, 2012 Mac OS X® 10.6 to 10.11 Linux 2.6.x to 4.4.x <i>LTS Versions only</i>
Power Consumption	.90mA
Power Source	USB-Powered
Humidity	0~80% RH Non-condensing
Operating Temperature	5°C to 40°C (41°F to 104°F)
Storage Temperature	-20°C to 70°C (-4°F to 158°F)
Color	Black
Product Length	10 ft [3 m]
Product Weight	7.1 oz [200 g]
Shipping (Package) Weight	0.8 lb [0.3 kg]
Included in Package	1 - USB to Parallel Converter Cable

Certifications, Reports and Compatibility

