

2 Port USB DisplayPort Cable KVM Switch w/ Audio and Remote Switch - USB Powered

StarTech ID: SV211DPUA



The SV211DPUA 2-Port DisplayPort® Cable KVM Switch with Audio and Remote Switching Control lets you control two DisplayPort, USB equipped PCs with a single monitor, keyboard, mouse and audio peripheral set.

To help organize your desk without sacrificing work space, this compact DisplayPort USB KVM features integrated cables that can be connected directly to your system, while leaving a minimal footprint. The switch features a remote push-button on a 1.5 meter (5ft) integrated cable that can be placed in an easily accessible location, as well as keyboard hot-keys, and PC or Mac® compatible software for switching between systems. To eliminate the need for a bulky external power adapter and wall outlet, the DisplayPort KVM switch is USB-powered.

This KVM with DisplayPort video capability offers support for resolutions up to 2560x1600 for the ability to drive a large DisplayPort display for applications that require high graphical output.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Great for PC test/burn-in computer control, saving the desk space required for two monitors, keyboards and mice
- Perfect for sharing computers and attached peripherals in the home or home office
- Dual system control for single user workstations increasing user productivity in the office

Features

- Supports resolutions up to 2560x1600
- Switch PCs via push-button, hot-keys or switching software
- Space-saving design, minimal footprint
- Integrated KVM cables and remote switch
- Switching software supports PC and Mac® platforms
- USB Powered - No external power adapter required
- Independent audio/mic switching for uninterrupted audio
- Analog (3.5mm) and DisplayPort audio supported
- Supports hot-plugging
- Remote switch on 1.5m (5ft.) cable

Technical Specifications

Warranty	2 Years
Audio	Yes
Cables Included	Yes
Daisy-Chain	No
KVM Ports	2
Multi-Monitor	No
PC Interface	USB
PC Video Type	DisplayPort
Rack-Mountable	No
Audio Specifications	Analog (3.5mm) and DisplayPort audio supported
Hot-Key Selection	Yes
IP Control	No
Port Selection Support	Push Button, Hotkeys, and Software
Console Interface(s)	1 - DisplayPort (20 pin) Female
Console Interface(s)	2 - 3.5 mm Mini-Jack (3 Position)
Console Interface(s)	2 - USB A (4 pin)
Host Connectors	1 - DisplayPort (20 pin) Latching Male
Host Connectors	1 - USB A (4 pin) Male
Host Connectors	2 - 3.5 mm Mini-Jack (3 Position) Male
OS Compatibility	Windows® 10 (32/64bit), 8 / 8.1 (32/64bit), 7 (32/64), Vista(32/64), XP(32/64), 2000 Windows Server® 2012, 2008 R2, 2003(32/64) Mac OS 10.x (Tested up to 10.9), 9.x
Note	OS Compatibility refers to KVM software only - the KVM itself can be used without software on any platform
LED Indicators	1 - PC Selection indicator
Power Source	USB-Powered
Humidity	0~90% RH Non-Condensing
Operating Temperature	0°C to 40°C (32°F to 104°F)
Storage Temperature	-20°C to 60°C (4°F to 140°F)
Cable Length	33.5 in [850 mm]
Color	Black
Enclosure Type	Plastic

Product Height	0.9 in [23 mm]
Product Length	3.5 in [88 mm]
Product Weight	14.1 oz [400 g]
Product Width	2.6 in [66 mm]
Shipping (Package) Weight	19.4 oz [550 g]
Included in Package	1 - KVM Switch
Included in Package	1 - Software CD
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

