

2 Port Professional USB KVM Switch Kit with Cables

StarTech ID: SV231USBGB



The SV231SUBGB 2 Port Professional USB KVM Switch Kit with Cables offers simple control of 2 computers from a single monitor/display and USB peripheral set (keyboard, mouse).

The 2 Port KVM includes 2 USB KVM cables, for a complete out-of-the-box solution saving you time and money. An integrated 3 port USB hub allows you to share USB peripherals between computers as though they were connected directly. A compact form factor and rear-port connections minimizes disruption to your workspace.

This OS independent KVM supports resolutions up to 1920x1440, and provides a smooth operating experience in mixed (Windows/Mac/Linux) environments.

Backed by a StarTech.com 3-year warranty and free lifetime technical support.

Applications

- Dual system control for a single workstations increasing user productivity in the office
- Provide centralized control for multiple high-res Digital Signage server control
- Great for manufacturing line computer control, simplifying access to multiple systems
- Perfect for PC test/burn-in computer control saving the desk space required for two monitors, keyboards and mice

Features

- Control 2 computers from one USB keyboard/mouse/monitor
- Share 3 different USB peripherals using the integrated hub
- High 1920x1440 resolution capability
- Front panel push buttons for easy computer selection
- OS independent - No software or drivers required
- Supports keyboard and mouse plug and play
- Selectable auto scan time interval
- Supports DDC2B VGA monitors
- Universal Power Adapter with EU and UK prong types included

Technical Specifications

| | |
|----------------------------|---|
| Warranty | 3 Years |
| Audio | No |
| Cables Included | Yes |
| Daisy-Chain | No |
| KVM Ports | 2 |
| Multi-Monitor | No |
| PC Interface | USB |
| PC Video Type | VGA |
| Rack-Mountable | No |
| U Height | 1U |
| Auto Scan | 3, 8, 15 & 30 seconds |
| DVI Support | No |
| Hot-Key Selection | No |
| IP Control | No |
| Maximum Analog Resolutions | 1920x1440 |
| Maximum Cable Length | 5 m [16.4 ft] |
| Maximum Number of Users | 1 |
| Port Selection Support | Push Button |
| Console Interface(s) | 1 - VGA (15 pin; High Density D-Sub) Female |
| Console Interface(s) | 3 - USB A (4 pin) Female |
| Host Connectors | 2 - USB B (4 pin) Female |
| Host Connectors | 2 - VGA (15 pin; High Density D-Sub) Male |
| OS Compatibility | OS independent; No software or drivers required |
| Center Tip Polarity | Positive |
| Input Current | 0.4A |
| Input Voltage | 110 ~ 240 AC |
| Output Current | 2A |
| Output Voltage | 5 DC |
| Plug Type | N |
| Power Source | AC Adapter Included |
| Color | Black |
| Enclosure Type | Steel |
| Product Depth | 70 mm [2.8 in] |

| | |
|---------------------------|-------------------------------------|
| Product Height | 40 mm [1.6 in] |
| Product Weight | 420 g [14.8 oz] |
| Product Width | 124 mm [4.9 in] |
| Shipping (Package) Weight | 1.5 kg [3.3 lb] |
| Included in Package | 1 - 2 Port KVM Switch |
| Included in Package | 2 - 6ft(1.83m) KVM Cables |
| Included in Package | 1 - Universal power adapter (EU/UK) |
| Included in Package | 1 - User Manual |

Certifications, Reports and Compatibility

