

Single-Monitor Stand - Silver - Works with Apple iMac & Apple Cinema Display

StarTech ID: ARMPIVSTND



The adjustable monitor stand lets you mount a display on your desk, with tilt, pivot and height adjustments for perfect positioning. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.



The monitor stand holds most common displays with ease, supporting monitors from 12 - 30" up to a maximum weight capacity of 30lbs (14kg). For added flexibility, the included hardware can be used to mount your Apple®

iMac® or Apple Cinema Display®.

The desktop monitor stand features a 15in (380mm) tall support post, for a much greater range of height adjustments than typical monitor stands can provide. For viewing longer pages or blocks of code without scrolling, the LCD stand also supports landscape to portrait display rotation.

Adjust your display height, position and viewing angles easily to create an ergonomic work environment, with the added benefit of reclaiming valuable workspace on your desk by mounting on a support post above the desk surface.

The ARMPIVSTND is backed by a StarTech.com 2-year warranty and free, lifetime technical support.

Applications

- Mount a display on your desk or table with tilt, swivel and height adjustment capabilities
- Lift your display higher above your desk surface for ideal viewing angles
- Rotate your display to portrait orientation for web design and coding

Features

- Adjustable monitor stand with several position / viewing angle adjustments
- Supports displays from 12 to 30" (30lbs / 14kg capacity)
- TAA compliant for GSA Schedule purchases
- Includes hardware for mounting an iMac or Apple Cinema Display
- Mounting bracket pans 60° around the support post
- Landscape-to-portrait screen rotation

Technical Specifications

Warranty	2 Years
# of displays supported	1
Mounting Options	Stand
One-touch height adjustment	No
VESA Hole Pattern(s)	75x75 mm
VESA Hole Pattern(s)	100x100 mm
Wallmountable	No
Display Rotation	360°
Height Adjustment	Yes
Maximum Display Size	30in
Pan	60°
Tilt	+45° / -15°
Weight Capacity	30.9 lb [14 kg]
Color	Silver
Enclosure Type	Steel and Plastic
Product Weight	6 lb [2.7 kg]
Shipping (Package) Weight	7.4 lb [3.3 kg]
Included in Package	1 - Aluminum Base
Included in Package	1 - Support Post
Included in Package	1 - Monitor Mount
Included in Package	1 - Cable Clip
Included in Package	1 - Iron Position Ring
Included in Package	4 - M5x18mm Hex Screws
Included in Package	1 - Flange
Included in Package	4 - Plastic Caps
Included in Package	1 - Torx Tool
Included in Package	1 - 3mm Allen Wrench
Included in Package	1 - 4mm Allen Wrench
Included in Package	1 - Access Card
Included in Package	4 - Thumb Screws
Included in Package	2 - M6x16mm Screws
Included in Package	4 - Rubber Feet
Included in Package	1 - Instruction manual

Certifications, Reports and Compatibility

