

2-port KVM Switch with Dual VGA - USB 2.0

StarTech ID: SV231DVGAU2A



This USB KVM lets you connect two computers, each with dual VGA outputs, to a dual-monitor workstation. You can switch the workstation between each computer, as well as two additional USB peripheral devices and 3.5mm speakers & microphone.

Maximize productivity with dual video

With support for two VGA video inputs and two different computers, this KVM switch maximizes productivity. Not only can you access multiple computers, but you can also use two VGA monitors on each computer streaming independent content to each display, which gives you the freedom to multitask and increase your productivity. The VGA ports support resolutions up to 1920x1200 for maximum screen viewing space.

Multi-system access

Featuring dual video and support for your keyboard and mouse, along with a 2-port USB hub for two additional peripheral devices, this KVM switch is perfect for accessing two separate systems using the same workstation. Support for your workstation plus two additional peripheral devices makes this KVM ideal for server control, simplifying access to multiple computer systems.

Hassle-free operation

This 2-port KVM ensures effortless operation with intuitive hotkey control. It provides a simple yet comprehensive solution for switching between each connected computer and also supports manual operation using the easy-to-access buttons located on the front of the switch.

The SV231DVGAU2A is backed by a 2-year StarTech.com warranty and free lifetime technical support.

Applications

- Control two computers each with dual-head video cards, from a single workstation, to increase your productivity at the office
- Work with multimedia applications such as video and photo editing
- Operate multiple computers in manufacturing lines
- Install in your server room, for multi-computer access

Features

- Maximum productivity with dual-display and multi-computer access
- Hassle-free operation with hotkey and push-button switching
- Share your USB peripheral devices with built-in 2-port USB hub
- Supports resolutions up to 1920x1200
- 3.5mm speaker and microphone console support

Technical Specifications

Warranty	2 Years
Audio	Yes
Cables Included	No
Daisy-Chain	No
KVM Ports	2
Multi-Monitor	Yes
PC Interface	USB
PC Video Type	VGA
Rack-Mountable	Optional
DVI Support	No
Hot-Key Selection	Yes
IP Control	No
Maximum Analog Resolutions	1920 x 1200
Maximum Number of Users	1
MTBF	72000 hours
Port Selection Support	Push Button and Hotkeys
Supported Resolutions	up to 1920 x 1200
Console Interface(s)	2 - VGA (15 pin; High Density D-Sub) Female Output
Console Interface(s)	1 - 3.5 mm Mini-Jack (3 Position) Female Output
Console Interface(s)	4 - USB A (4 pin) Female
Host Connectors	4 - VGA (15 pin; High Density D-Sub) Female Input
Host Connectors	4 - 3.5 mm Mini-Jack (3 Position) Female Input
Host Connectors	2 - USB B (4 pin) Female
LED Indicators	1 - Green - Power
LED Indicators	2 - Green - PC Detected
LED Indicators	2 - PC Selection Indicators
LED Indicators	2 - Red - PC Indicator
Center Tip Polarity	Positive
Input Current	0.8A
Input Voltage	110 ~ 240 AC
Output Current	1.5A
Output Voltage	12 DC
Plug Type	M

Power Source	AC Adapter Included
Humidity	90% RH
Operating Temperature	0°C to 40°C (32°F to 104°F)
Storage Temperature	-20°C to 60°C (-4°F to 140°F)
Color	Black
Enclosure Type	Steel
Product Depth	5.1 in [130 mm]
Product Height	2.2 in [57 mm]
Product Length	6.3 in [159 mm]
Product Weight	27 oz [765 g]
Product Width	4.1 in [104 mm]
Shipping (Package) Weight	2.6 lb [1.2 kg]
Included in Package	1 - dual VGA USB KVM switch
Included in Package	1 - universal power adapter (NA / EU / UK / AU)
Included in Package	1 - instruction manual

Certifications, Reports and Compatibility

