

## **12U 19in Desktop Open Frame 2 Post Rack**

*StarTech ID: RK12OD*



The RK12OD 12U 19in Desktop Open Frame 2 Post Rack provides the perfect mounting option for smaller Audio/Video and IT equipment where space is limited and a full sized cabinet is not required. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

The 12U rack features a compact and lightweight free-standing design that is suitable for installation on or around your desk giving you easy access to the mounted equipment in your workspace. This lightweight 2 post rack is engineered to meet EIA rack mount standards and includes a pack of 20 M5 screws and Cage Nuts, allowing you to mount up to five devices into the rack right away.

Backed by a StarTech.com lifetime warranty.

### **Applications**

- Mount patch panels, network switches, and routers in small or home office networks or IT offices to provide easy access to equipment
- Mount KVMs and rack-mount computer/server systems neatly on or beside your desk
- Mount AV equipment such as broadcast/distribution devices, switches or extenders

## Features

- Includes 20 M5 Screws and Cage Nuts for mounting devices
- Easy to assemble
- TAA compliant for GSA Schedule purchases
- Lightweight design for easy relocation
- Meets EIA standards

## Technical Specifications

|                           |                                             |
|---------------------------|---------------------------------------------|
| Warranty                  | Lifetime                                    |
| Fan(s)                    | No                                          |
| Frame Type                | Open Frame                                  |
| Front Door Type           | Open                                        |
| Industry Standards        | EIA RS310-C                                 |
| Rack Type                 | 2-Post                                      |
| U Height                  | 12U                                         |
| Wallmountable             | No                                          |
| Weight Capacity           | 110.5 lb [50 kg]                            |
| Color                     | Black                                       |
| External Depth            | 11.5 in [292 mm]                            |
| External Height           | 23 in [584.4 mm]                            |
| External Width            | 19.8 in [504 mm]                            |
| Internal Width            | 17.8 in [451 mm]                            |
| Product Weight            | 95 oz [2690 g]                              |
| Flat Pack                 | Yes                                         |
| Shipping (Package) Weight | 6.7 lb [3 kg]                               |
| Included in Package       | 2 - 12U Vertical Post                       |
| Included in Package       | 2 - Legs                                    |
| Included in Package       | 1 - Base Bracket                            |
| Included in Package       | 1 - Package of assembly hardware (8 Screws) |
| Included in Package       | 20 - M5 Screws, and Cage Nuts               |
| Included in Package       | 4 - Rubber Feet                             |

Certifications, Reports and Compatibility

