

3U 19in Steel Vertical Wall Mount Equipment Rack Bracket

StarTech ID: RK319WALLV



The RK319WALLV 3U 19in Steel Vertical Wall Mount Equipment Rack Bracket offers a versatile storage solution, allowing equipment (Network devices, power strips, patch panels) to be mounted vertically (flush with wall) to save space. Alternatively, the 3U bracket can be installed under a desk for horizontal installation, making it easy to access installed equipment directly from your workspace. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

Constructed to EIA-310 19in rack standards, the wallmount bracket features a sturdy steel design, perfect for SoHo (small office, home office) environments. The wallmount bracket offers space-saving installation for environments lacking the footprint space for a full size server equipment rack.

Suitable for mounting on virtually any wall/ceiling surface (e.g. drywall), the bracket mounting holes (used to mount to a wall or the desk underside) are positioned at exactly 16in apart, matching standard construction framework.

Backed by a StarTech.com lifetime warranty.

Need more storage space? StarTech.com also offers a [1U 19in Wallmount Bracket](#), a [2U 19in Wallmount Bracket](#) and a [4U 19in Wallmount Bracket](#).

Applications

- Mount networking and telecommunication equipment flush against the wall
- Mount KVM switches or workstations under a desk or work bench to free up work space
- Ideal for small and medium businesses needing rack solutions

Features

- Constructed to meet the EIA-310 19" rack standards
- Arrives fully assembled with cage screws and nuts for mounting equipment into the rack
- TAA compliant for GSA Schedule purchases
- Equipment can be vertically wall mounted, or horizontally under a desk
- Compatible with most 19" rack mountable equipment
- Made from solid steel for durability
- Wall mounting holes are 16" center to center for greater stability, and mounting to standard wall studs

Technical Specifications

Warranty	Lifetime
Fan(s)	No
Frame Type	Open Frame
Front Door Type	Open
Industry Standards	EIA RS310-C
Rack Type	2-Post
U Height	3U
Wallmountable	Yes
Weight Capacity	125.3 lb [56.7 kg]
Note	Package includes 1 ½" screws for mounting to wood surfaces, additional hardware will be required for other materials
Color	Black
External Depth	5.9 in [151 mm]
External Height	5.9 in [149 mm]
External Width	19.8 in [504 mm]
Internal Width	18.3 in [465 mm]
Product Weight	33.2 oz [940 g]
Flat Pack	No
Shipping (Package Weight)	3.1 lb [1.4 kg]
Included in Package	1 - Vertical Wall Mount Bracket
Included in Package	12 - Cage nuts and screws (12 Each)
Included in Package	6 - Self Tapping Wood Screws - 3/16" x 1 1/2"

Certifications, Reports and Compatibility

