

## 4U 19in Steel Vertical Wall Mount Equipment Rack Bracket

StarTech ID: RK419WALLV



The RK419WALLV 4U Wallmount Rack Bracket offers a versatile storage solution, allowing equipment (Network devices, power strips, patch panels) to be mounted vertically (flush with the wall) to save space. Alternatively, the 4U bracket can be installed under a desk for horizontal installation, making it easy to access installed equipment directly from your workspace. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

Perfect for SoHo (small office, home office) environments, the wallmount bracket offers space-saving installation for environments lacking the footprint space for a full size server equipment rack.

Suitable for mounting on virtually any wall/ceiling surface (e.g. drywall), the bracket mounting holes (used to mount to a wall or the desk underside) are positioned at exactly 16in apart, matching standard construction framework.

Constructed to EIA-310 19in rack standards, the wallmount bracket features a sturdy steel design and is backed by StarTech.com's Lifetime Warranty.

Need more storage space? StarTech.com also offers a [1U 19in Wallmount Bracket](#), a [2U 19in Wallmount Bracket](#) and a [3U 19in Wallmount Bracket](#).

### Applications

- Mount networking and telecommunication equipment flush against the wall
- Mount KVM switches or workstations under a desk or work bench to free up work space
- Ideal for small and medium businesses needing rack solutions

## Features

- 4U Wallmount design
- Equipment can be vertically wall mounted, or horizontally under a desk
- TAA compliant for GSA Schedule purchases
- Arrives fully assembled with cage screws and nuts for mounting equipment
- Wall mounting holes are 16" center to center for greater stability, and mounting to standard wall studs
- Constructed to meet the EIA-310 19" rack standards
- Made from solid steel for durability

## Technical Specifications

Warranty	Lifetime
Fan(s)	No
Frame Type	Open Frame
Front Door Type	Open
Industry Standards	EIA RS310-C
Rack Type	2-Post
U Height	4U
Wallmountable	Yes
Weight Capacity	125.3 lb [56.7 kg]
<b>Note</b>	Package includes 1½" screws for mounting to wood surfaces, additional hardware will be required for other materials
Color	Black
External Depth	7.6 in [193.5 mm]
External Height	5.9 in [151 mm]
External Width	19.8 in [504 mm]
Internal Width	17.7 in [450 mm]
Product Weight	37.4 oz [1060 g]
Flat Pack	No
Shipping (Package Weight)	2.5 lb [1.1 kg]
Included in Package	1 - Vertical Wall Mount Bracket
Included in Package	16 - Cage nuts and screws (16 Each)
Included in Package	6 - Self Tapping Wood Screws - 3/16" x 1 1/2"

Certifications, Reports and Compatibility

