


Data Sheet

3.5 mm right angle mono plug with 1.2 M cable



Drawing:



Technical data

Cable length: 1.20 m

The rate of conductivity is 100%

No short or open circuit is allowed, no circuit misplacement is allowed.

Conductor resistance < 1 Ω

Insulation resistance ≥ 20 MΩ

Voltage: 5 V DC

*Grind the soldering point of the copper head