



# Push-pull connectors female fixed socket CCB series



## CCB2S1/06 6 pole

- Premium range of circular connectors
- IP68 sealed using vacuum technology (when connected and using environmental cable clamp)
- Tough, high performance interconnection solution
- Compact panel mounting design
- Ideal for harsh and extreme environments
- Suitable for broadcasting, autosport, military, rail, marine, security, industrial and agricultural applications
- Key coded to prevent misconnection
- Will not disconnect when the cable is under load or stress
- Tested to IEC 60512-3-5a



CCB2S1/06



| PART NO.  | DESCRIPTION         | POLES | SERIES     |
|-----------|---------------------|-------|------------|
| CCB2S1/06 | Female fixed socket | 06    | CCB series |

### SPECIFICATION

|                         |   |
|-------------------------|---|
| Shell style/model       | D type fixed socket, female contact   |
| Codes                   | Code 1  |
| Contact type            | Solder type   |
| Contact diameter        | 0.7mm   |
| Max. stranded conductor | AWG 21-22   |
| Max diameter            | 0.79mm  |
| Vtest (contact-shell)   | 1000V(AC)<br>2000V(DC)  |
| Vtest (contact-contact) | 1300V(AC)<br>2000V(DC)  |
| Rated current           | 5.2A  |
| Rated voltage           | ≤250V   |
| Mechanical operation    | 5000 mating cycles  |
| Housing material        | Brass (natural chrome plated) shell and collet nut, nickel plated brass latch sleeve and mid pieces |
| Insulator               | PPS   |
| Contacts                | Brass (gold plated)   |
| Humidity (max)          | ≤95% [at 60°C /140°F]   |
| Vibration               | 15g [10 Hz - 2000 Hz]   |
| Shock resistance        | 100g [6 ms]   |
| Salt spray corrosion    | >72 hr  |
| Climatical category     | 50/175/21   |
| Shielding (min)         | 75 dB (10 MHz)  |
| Shielding (min)         | 40 dB (1 GHz)   |
| IP rating               | IP68 (when connected and using environmental cable clamp)   |



## KEY FEATURES

Key coded | Panel mounting socket | Flat face | Low profile

## ACCESSORIES

Metal and rubber caps for sockets

| PART NO. | DESCRIPTION                          |
|----------|--------------------------------------|
| CCT21    | Camcircular metal cap for sockets A2 |



| PART NO. | DESCRIPTION                           |
|----------|---------------------------------------|
| CCT22    | Camcircular rubber cap for sockets A2 |



## ASSOCIATED PRODUCTS

CCA2P1/A06

- CCA Series A2 size plug

page 110

002  
PCB TERMINAL  
BLOCKS

081  
TERMINAL STRIPS

095  
WIRE TO BOARD  
CONNECTORS

100  
CIRCULAR  
CONNECTORS

151  
IP68 CONNECTORS

158  
INTERFACE  
MODULES AND  
RELAY BASES

CONNECT

135



+44 (0)1638 716101 | sales@camdenboss.com | www.camdenboss.com

We operate a constant improvement policy, our products are subject to change without notice.

Vers 1