100 CIRCULAR CONNECTORS

CANCIRU SIRGULAR TO CONNECTOR

Push-pull connectors cable mounted plug CCA2 series

CCA2P1/A03 3 pole

- Premium range of circular connectors
- IP68 sealed using vacuum technology (when connected and using environmental cable clamp)
- Tough, high performance interconnection solution
- Ideal for harsh and extreme environments
- Suitable for broadcasting, autosport, military, rail, marine, security, industrial and agricultural applications
- Key coded to prevent misconnection
- Will not disconnect when the cable is under load or stress
- Tested to IEC 60512-3-5a



| PART NO. | DESCRIPTION | POLES | SERIES |
|------------|--------------------|-------|------------|
| CCA2P1/A03 | Cable mounted plug | 3 | CCA series |


| ~46 ~35 ~35 ~30 ~30 ~30 ~30 ~30 ~30 ~30 ~30 ~30 ~30 |
|---|
| |

| SPECIFICATION | | | | |
|-------------------------|--|--|--|--|
| Shell style/model | Cable mounted straight plug, male contact | | | |
| Codes | Code 1 | | | |
| Contact type | Solder type | | | |
| Contact diameter | 1.18mm | | | |
| Max. stranded conductor | AWG 17-18 | | | |
| Max diameter | 0.43mm | | | |
| Vtest (contact-shell) | 1200V(AC) 1800V(DC) | | | |
| Vtest (contact-contact) | 1500V(AC) 2000V(DC) | | | |
| Rated current | 12A | | | |
| Rated voltage | ≤250V | | | |
| Mechanical operation | 5000 mating cycles | | | |
| Housing material | Brass (natural chrome plated) shell and collet nut, nickel plated brass latch sleeve and mid pieces | | | |
| Insulator | PPS | | | |
| Contacts | Brass (gold plated) | | | |
| Humidity (max) | <=95% [at 60°C /140°F] | | | |
| Vibration | 15g [10 Hz - 2000 Hz] | | | |
| Shock resistance | 100g [6 ms] | | | |
| Salt spray corrosion | >72 hr | | | |
| Climatical category | 50/175/21 | | | |
| Shielding (min) | 75 dB (10 MHz) | | | |
| Shielding (min) | 40 dB (1 GHz) | | | |
| IP rating | IP68 (when connected and using environmental cable clamp) | | | |

This product should be used with the following cable clamps:

| PART NO. | WIRE RANGE |
|----------|-------------|
| CCV2C/CE | 3.7 - 4.2mm |
| CCV2C/CG | 4.2 - 4.7mm |
| CCV2C/CH | 4.7 - 5.2mm |
| CCV2C/CI | 5.2 - 5.7mm |
| CCV2C/CJ | 5.7 - 6.2mm |





Non IP68 cable clamps also available

ACCESSORIES

Metal cap for plugs

| PART NO. | DESCRIPTION |
|----------|-------------------------------|
| CCA22 | Camcirc metal cap for plug A2 |
| | |



ASSOCIATED PRODUCTS

CCB2S1/03

-CCB series A2 size socket

page 133

107