




MOUNTING HOLE LAYOUT



仕様
SPECIFICATION



耐電圧 : AC250V 1分間
 DIELECTRIC STRENGTH:500V AC FOR ONE MINUTE.
 接触抵抗 : 50mΩ以下
 CONTACT RESISTANCE:50mΩ MAX
 絶縁抵抗 : DC250Vにて100MΩ以上
 INSULATION RESISTANCE:100MΩ MIN. AT 500V DC.

PART NAME	QTY	MATERIAL	PLATING	REMARKS
BODY	1	P. C. +G.		BLACK
METAL	1	BsBM2 6PHI	Ni-3	
MAIN TERMINAL A	1	BsR2-H 0.25t	Ag	(TIP CONTACT)
MAIN TERMINAL B	1	PBSR-EH 0.25t	Ag	(RING CONTACT)
EARTH TERMINAL	1	BsR2-H 0.3t	Ag	(SLEEVE CONTACT)
SPRING (A)	1	SUS-304		HEAT TREATMENT

P/N: MJ-355W w/THREAD 3.5mm STEREO JACK Unit: mm Tol.: +/-0.3

CUSTOMER:

CUSTOMER P/N:

DATE: 1998/04/10