

Specifications:

- Rating 12V, 10A Max.
- Contact resistance 100mΩ Max.
- Insulation resistance DC 500V 100MΩ Min.
- Voltage breakdown 1000V AC for 1 minute
- Operating temperature -20°C ~ +65°C

